

19" Fan Unit, 1 U

Fan Unit for installation into a 1U space within the Cabinet.



CERTIFICERINGER



FUNKTIONER

Mechanical strain relief for mains cables

Can be adapted to subracks

Contact protection in accordance with DIN EN ISO 13857

SPECIFIKATIONER

Table 1/1

Katalognummer	Indgangsspænding AC	Indgangsspænding DC	Pakke mængde	Finish	Materiale
10713-100	230V		1	Aluminum-Zinc Plated, Anodized	Stål, Aluminium
10713-107		24V min	1	Aluminum-Zinc Plated, Anodized	Stål, Aluminium
10713-106	115V		1	Aluminum-Zinc Plated, Anodized	Stål, Aluminium
10713-104	230V		1	Aluminum-Zinc Plated, Anodized	Stål, Aluminium

Katalognummer	Indgangsspænding AC	Indgangsspænding DC	Pakke mængde	Finish	Materiale
10713-102	115V		1	Aluminum-Zinc Plated, Anodized	Stål, Aluminium
10713-103		24V min	1	Aluminum-Zinc Plated, Anodized	Stål, Aluminium

YDERLIGERE PRODUKTOPLYSNINGER

Please order mains cable separately.

Wide-range input voltage (86 ... 264 VAC) available on request.

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Vores kraftfulde portefølje af mærker:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE