

CompacPRO Tip-Up Handle

Tip-up carrying handle.



CERTIFICERINGER



FUNKTIONER

Load-carrying capacity 20 kg

Carrying bar adjustable in increments of 30° by push button

With powder-coated carrying bar

The handle enable a user to have a better view to the front side of the case in case of desktop usage

SPECIFIKATIONER

- Works With:** Cases
Produktfamilie: CompacPRO
Product Type: Handle

Table 1/1

Katalognummer	Rack Width	Pakke mængde	Håndtagstype	Length	Materiale
24575-038	42HP	1	Tip-up Handle	180mm	Aluminium, Zinc Alloy
24575-178	84HP	1	Tip-up Handle	180mm	Aluminium, Zinc Alloy

Katalognummer	Rack Width	Pakke mængde	Håndtagstype	Length	Materiale
24575-158	63HP	1	Tip-up Handle	180mm	Aluminium, Zinc Alloy
24575-138	42HP	1	Tip-up Handle	180mm	Aluminium, Zinc Alloy
24575-118	28HP	1	Tip-up Handle	180mm	Aluminium, Zinc Alloy
24575-078	84HP	1	Tip-up Handle	180mm	Aluminium, Zinc Alloy

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden unladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Vores kraftfulde portefølje af mærker:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE