

# Varistar CP Rear Panel, Screw Fixed

## Data Solutions



Cabinets have rear panels well screwed to the frame to have maximum contact with the gasket.

### FUNKTIONER

Screw fixed, Robust and Single person mountable Side Panel

Rear panel without grounding kit

### SPECIFIKATIONER

**Product Type:** Cabinet/Rack Panel

**Materiale:** Stål

Table 1/2

Katalognummer	Rack Height	Højde	Bredde	Beskyttelsesgrad	Pakke mængde	Farve
21630-199	29U	1400mm	600mm	IP55	1	Black Grey
21630-384	24U	1200mm	600mm	IP20	1	Black Grey
21630-551	38U	1800mm	600mm	IP55	1	
21630-124	52U	2450mm	600mm	IP20	1	Black Grey
21630-385	24U	1200mm	800mm	IP20	1	Black Grey
21630-200	33U	1600mm	600mm	IP55	1	Black Grey
21630-549	33U	1600mm	600mm	IP55	1	
21630-386	29U	1400mm	600mm	IP20	1	Black Grey
21630-125	42U	2000mm	800mm	IP20	1	Black Grey

Katalognummer	Rack Height	Højde	Bredde	Beskyttelsesgrad	Pakke mængde	Farve
21630-387	29U	1400mm	800mm	IP20	1	Black Grey
21630-548	29U	1400mm	800mm	IP55	1	
21630-550	33U	1600mm	800mm	IP55	1	
21630-547	29U	1400mm	600mm	IP55	1	
21630-388	33U	1600mm	600mm	IP20	1	Black Grey
21630-389	33U	1600mm	800mm	IP20	1	Black Grey
21630-126	47U	2200mm	800mm	IP20	1	Black Grey
21630-546	24U	1200mm	800mm	IP55	1	
21630-198	24U	1200mm	600mm	IP55	1	Black Grey
21630-545	24U	1200mm	600mm	IP55	1	
21630-390	38U	1800mm	600mm	IP20	1	Black Grey

Table 2/2

Katalognummer	Rack Height	Højde	Bredde	Beskyttelsesgrad	Pakke mængde	Farve
21630-391	38U	1800mm	800mm	IP20	1	Black Grey
21630-127	52U	2450mm	800mm	IP20	1	Black Grey
21630-122	42U	2000mm	600mm	IP20	1	Black Grey
21630-206	33U	1600mm	800mm	IP55	1	Black Grey
21630-202	42U	2000mm	600mm	IP55	1	Black Grey
21630-207	38U	1800mm	800mm	IP55	1	Black Grey
21630-554	42U	2000mm	800mm	IP55	1	
21630-205	29U	1400mm	800mm	IP55	1	Black Grey
21630-123	47U	2200mm	600mm	IP20	1	Black Grey
21630-555	47U	2200mm	600mm	IP55	1	
21630-203	47U	2200mm	600mm	IP55	1	Black Grey
21630-553	42U	2000mm	600mm	IP55	1	
21630-556	47U	2200mm	800mm	IP55	1	
21630-204	24U	1200mm	800mm	IP55	1	Black Grey
21630-208	42U	2000mm	800mm	IP55	1	Black Grey
21630-209	47U	2200mm	800mm	IP55	1	Black Grey
21630-552	38U	1800mm	800mm	IP55	1	
21630-201	38U	1800mm	600mm	IP55	1	Black Grey

Table 1/2

Katalognummer	Farvekode	Finish	Type	Works With
21630-199	RAL 7021	Struktur Pulvermaling	Rear Panel	Varistar CP
21630-384	RAL 7021	Struktur Pulvermaling	Rear Panel	Varistar CP
21630-551		Struktur Pulvermaling	Rear Panel	Varistar CP
21630-124	RAL 7021	Struktur Pulvermaling	Rear Panel	Varistar CP
21630-385	RAL 7021	Struktur Pulvermaling	Rear Panel	Varistar CP
21630-200	RAL 7021	Struktur Pulvermaling	Rear Panel	Varistar CP
21630-549		Struktur Pulvermaling	Rear Panel	Varistar CP
21630-386	RAL 7021	Struktur Pulvermaling	Rear Panel	Varistar CP
21630-125	RAL 7021	Struktur Pulvermaling	Rear Panel	Varistar CP
21630-387	RAL 7021	Struktur Pulvermaling	Rear Panel	Varistar CP
21630-548		Struktur Pulvermaling	Rear Panel	Varistar CP
21630-550		Struktur Pulvermaling	Rear Panel	Varistar CP
21630-547		Struktur Pulvermaling	Rear Panel	Varistar CP
21630-388	RAL 7021	Struktur Pulvermaling	Rear Panel	Varistar CP
21630-389	RAL 7021	Struktur Pulvermaling	Rear Panel	Varistar CP
21630-126	RAL 7021	Struktur Pulvermaling	Rear Panel	Varistar CP
21630-546		Struktur Pulvermaling	Rear Panel	Varistar CP
21630-198	RAL 7021	Struktur Pulvermaling	Rear Panel	Varistar CP
21630-545		Struktur Pulvermaling	Rear Panel	Varistar CP
21630-390	RAL 7021	Struktur Pulvermaling	Rear Panel	Varistar CP

Table 2/2

Katalognummer	Farvekode	Finish	Type	Works With
21630-391	RAL 7021	Struktur Pulvermaling	Rear Panel	Varistar CP
21630-127	RAL 7021	Struktur Pulvermaling	Rear Panel	Varistar CP
21630-122	RAL 7021	Struktur Pulvermaling	Rear Panel	Varistar CP
21630-206	RAL 7021	Struktur Pulvermaling	Rear Panel	Varistar CP
21630-202	RAL 7021	Struktur Pulvermaling	Rear Panel	Varistar CP
21630-207	RAL 7021	Struktur Pulvermaling	Rear Panel	Varistar CP
21630-554		Struktur Pulvermaling	Rear Panel	Varistar CP
21630-205	RAL 7021	Struktur Pulvermaling	Rear Panel	Varistar CP
21630-123	RAL 7021	Struktur Pulvermaling	Rear Panel	Varistar CP
21630-555		Struktur Pulvermaling	Rear Panel	Varistar CP
21630-203	RAL 7021	Struktur Pulvermaling	Rear Panel	Varistar CP
21630-553		Struktur Pulvermaling	Rear Panel	Varistar CP

Katalognummer	Farvekode	Finish	Type	Works With
21630-556		Struktur Pulvermaling	Rear Panel	Varistar CP
21630-204	RAL 7021	Struktur Pulvermaling	Rear Panel	Varistar CP
21630-208	RAL 7021	Struktur Pulvermaling	Rear Panel	Varistar CP
21630-209	RAL 7021	Struktur Pulvermaling	Rear Panel	Varistar CP
21630-552		Struktur Pulvermaling	Rear Panel	Varistar CP
21630-201	RAL 7021	Struktur Pulvermaling	Rear Panel	Varistar CP

## YDERLIGERE PRODUKTOPLYSNINGER

---

Please purchase the grounding kit separately.

## ADVARSEL

---

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på [www.nvent.com](http://www.nvent.com) og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.



Vores kraftfulde portefølje af mærker:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**