


# Backplane With Through-Connected Signal Lines

Backplane with Through Connected Signal Lines.



## CERTIFICERINGER



## FUNKTIONER

Power supply at each connector position (row 1 + 32)

Adaptation fields for power connections on 2-layer backplanes

## SPECIFIKATIONER

Table 1/2

Katalognummer	Product Type	Number of Slots	Rack Height	Backplane Type	Slot Width	Connector Type
23007-421	Backplane	21	3U	90 Signal Lines	4HP	C96F
23007-051	Backplane	21	3U	60 Signal Lines	4HP	C96F
23007-040	Backplane	10	3U	60 Signal Lines	4HP	C96F
23007-410	Backplane	10	3U	90 Signal Lines	4HP	C96F
23007-188	Backplane	28	3U	60 Signal Lines	3HP	
23007-010	Backplane	10	3U	60 Signal Lines	4HP	C64F
23007-081	Backplane	21	3U	60 Signal Lines	4HP	

Katalognummer	Product Type	Number of Slots	Rack Height	Backplane Type	Slot Width	Connector Type
23007-114	Backplane	14	3U	60 Signal Lines	3HP	C64F
23007-158	Backplane	28	3U	60 Signal Lines	3HP	C96F
23007-128	Backplane	28	3U	60 Signal Lines	3HP	C64F
23007-021	Backplane	21	3U	60 Signal Lines	4HP	C64F

Table 2/2

Katalognummer	Power Connector Type	Pakke mængde
23007-421	Fastons 6.3 x 0.8 mm	1
23007-051	Fastons 6.3 x 0.8 mm	1
23007-040	Fastons 6.3 x 0.8 mm	1
23007-410	Fastons 6.3 x 0.8 mm	1
23007-188	Fastons 6.3 x 0.8 mm	1
23007-010	Fastons 6.3 x 0.8 mm	1
23007-081	Fastons 6.3 x 0.8 mm	1
23007-114	Fastons 6.3 x 0.8 mm	1
23007-158	Fastons 6.3 x 0.8 mm	1
23007-128	Fastons 6.3 x 0.8 mm	1
23007-021	Fastons 6.3 x 0.8 mm	1

## ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på [www.nvent.com](http://www.nvent.com) og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden unkladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Vores kraftfulde portefølje af mærker:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**