

Interscale Desktop Case, Non-Perforated

Flexible desktop case with integrated EMC protection.
Based on the nVent SCHROFF Interscale platform and developed in accordance with IEC 60297-3-109.



CERTIFICERINGER



FUNKTIONER

Modular desktop case consisting of 4 assembled parts

Developed according to IEC 60297-3-109 (under progress at IEC)

Integrated EMC protection

Ingress protection up to IP 30

Color RAL 7016

Modified or customized cases upon request

SPECIFIKATIONER

Materiale:	Aluminium; Stål
Type:	Desktop
Produktfamilie:	Interscale
Beskyttelsesgrad:	IP30
Farvekode:	RAL 7016
Product Type:	Small Form Factor Case

Table 1/2

Katalognummer	Højde	Pakke mængde	Bredde	Dybde	Cooling	Farve
14820-133	43.7mm	1	132.6mm	132.6mm	Non-Perforated	Anthracite Grey
14820-297	88.1mm	1	399mm	310.35mm	Non-Perforated	Anthracite Grey
14820-255	88.1mm	1	221mm	221.45mm	Non-Perforated	Anthracite Grey
14820-295	88.1mm	1	399mm	221.45mm	Non-Perforated	Anthracite Grey
14820-154	43.7mm	1	221mm	177mm	Non-Perforated	Anthracite Grey
14820-375	132.6mm	1	310mm	221.45mm	Non-Perforated	Anthracite Grey
14820-254	88.1mm	1	221mm	177mm	Non-Perforated	Anthracite Grey
14820-155	43.7mm	1	221mm	221.45mm	Non-Perforated	Anthracite Grey
14820-395	132.6mm	1	399mm	221.45mm	Non-Perforated	Anthracite Grey
14820-134	43.7mm	1	133mm	177mm	Non-Perforated	Anthracite Grey
14820-195	43.7mm	1	399mm	221.45mm	Non-Perforated	Anthracite Grey
14820-175	43.7mm	1	310mm	221.45mm	Non-Perforated	Anthracite Grey
14820-275	88.1mm	1	310mm	221.45mm	Non-Perforated	Anthracite Grey
14820-397	132.6mm	1	399mm	310.35mm	Non-Perforated	Anthracite Grey
14820-197	43.7mm	1	399mm	310.35mm	Non-Perforated	Anthracite Grey

Table 2/2

Katalognummer	Finish
14820-133	Aluminum-Zinc Plated, Struktur Pulvermaling
14820-297	Aluminum-Zinc Plated, Struktur Pulvermaling
14820-255	Aluminum-Zinc Plated, Struktur Pulvermaling
14820-295	Aluminum-Zinc Plated, Struktur Pulvermaling
14820-154	Aluminum-Zinc Plated, Struktur Pulvermaling
14820-375	Aluminum-Zinc Plated, Struktur Pulvermaling
14820-254	Aluminum-Zinc Plated, Struktur Pulvermaling
14820-155	Aluminum-Zinc Plated, Struktur Pulvermaling
14820-395	Aluminum-Zinc Plated, Struktur Pulvermaling
14820-134	Aluminum-Zinc Plated, Struktur Pulvermaling
14820-195	Aluminum-Zinc Plated, Struktur Pulvermaling
14820-175	Aluminum-Zinc Plated, Struktur Pulvermaling
14820-275	Aluminum-Zinc Plated, Struktur Pulvermaling
14820-397	Aluminum-Zinc Plated, Struktur Pulvermaling
14820-197	Aluminum-Zinc Plated, Struktur Pulvermaling

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden unndladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Vores kraftfulde portefølje af mærker:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE