

# Socket Strip, IEC C13

Modular, compact PDU with many function elements. Using a 1 U by 1 U aluminum chassis the PDU can easily be integrated in a rack with IEC C13 outlets.



## CERTIFICERINGER



## FUNKTIONER

230 V, 10 A

Horizontal and vertical mounting

Socket strips can be rotated through all four directions (in 90° increments) during installation

Socket strips with IEC 60320-C13 sockets

Connecting cable 2 m, open end with ferrules

In accordance with IEC 60320

Mounting height 1 U

## SPECIFIKATIONER

**Materiale:** Aluminium; Polyamide

**Farve:** Grey

**Product Type:** Socket Strip

Table 1/2

Katalognummer	Stiktype	Socket Quantity	Switched Outlets	Spænding AC	Pakke mængde	Dybde
60110-292	IEC C13	16	No	230V	1	44mm

Katalognummer	Stiktype	SocketQuantity	Switched Outlets	Spænding AC	Pakke mængde	Dybde
60110-290	IEC C13	8	No	230V	1	44mm
60110-291	IEC C13	12	No	230V	1	44mm

Table 2/2

Katalognummer	Finish	Length
60110-292	Anodized	608.5mm
60110-290	Anodized	438.5mm
60110-291	Anodized	438.5mm

## YDERLIGERE PRODUKTOPLYSNINGER

Please order bracket for vertical mounting separately.

## ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på [www.nvent.com](http://www.nvent.com) og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden unladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Vores kraftfulde portefølje af mærker:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**