


Minipac Trapezoid Shape Case, Wall Mount

KATALOGNUMMER

24814-010



The Trapezoid Alu-profile case enables a user to insert 3 non standard PCBs. The PCBs will be inserted in grooves in the Alu-profile tube. Both sides are covered with 2.5 mm thick L-shaped front panels for wall mounting.

CERTIFICERINGER



FUNKTIONER

Wall mounting

PCB thickness 1.6 mm, spacing 15.24 mm (3 HP)

Length D = 100 mm, width of long side 74.2 mm, width of short side 54.5 mm, height 46.1 mm

Accommodates 3 non-standardized PCBs (height 50, 60 and 65 mm, depth 100 mm)

PRODUKTEGENSKABER

Product Type: Small Form Factor Case

Produktfamilie: Minipac

Type: Wall Mount

Højde: 88.1mm

Bredde: 52mm

Dybde: 100.5mm

Materiale: Aluminium

Farve: Black

Finish: Anodized

Beskyttelsesgrad: IP40

Cooling: Non-Perforated

Shape: Trapezium

Pakke mængde: 1

Length: 100.5mm

Net Weight: 0.27kg

YDERLIGERE PRODUKTOPLYSNINGER

Other dimensions on request.

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Vores kraftfulde portefølje af mærker:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE