


Varistar Cable Panel



Vertical cable panel for Varistar free standing cabinets powdered in cabinet color in different widths.

CERTIFICERINGER



FUNKTIONER

For fitting directly onto the frame

Cables are assembled in place with cable ties or Velcro

SPECIFIKATIONER

Product Type: Cabinet/Rack Panel

Materiale: Stål

Table 1/2

Katalognummer	Rack Height	Højde	Bredde	Dybde	Pakke mængde	Farve
23130-625	52U	2450mm	250mm	250mm	2	Black Grey
23130-502		1019mm	110mm	10mm	2	Black Grey
23130-422	47U	2200mm	150mm	150mm	2	Black Grey
23130-501		446mm	110mm	10mm	2	Black Grey

Katalognummer	Rack Height	Højde	Bredde	Dybde	Pakke mængde	Farve
23130-503		670mm	110mm	10mm	2	Black Grey
23130-500		604mm	110mm	10mm	2	Black Grey
23130-504		496mm	110mm	10mm	2	Black Grey
23130-628	52U	2450mm	150mm	150mm	2	Black Grey
23130-420	38U	1800mm	150mm	150mm	2	Black Grey
23130-150	42U	2000mm	250mm	250mm	2	Black Grey
23130-151	47U	2200mm	250mm	250mm	2	Black Grey
23130-421	42U	2000mm	150mm	150mm	2	Black Grey
23130-499		915.5mm	110mm	10mm	2	Black Grey

Table 2/2

Katalognummer	Farvekode	Finish	Type
23130-625	RAL 7021	Struktur Pulvermaling	Cable Panel
23130-502	RAL 7021	Struktur Pulvermaling	Cable Panel
23130-422	RAL 7021	Struktur Pulvermaling	Cable Panel
23130-501	RAL 7021	Struktur Pulvermaling	Cable Panel
23130-503	RAL 7021	Struktur Pulvermaling	Cable Panel
23130-500	RAL 7021	Struktur Pulvermaling	Cable Panel
23130-504	RAL 7021	Struktur Pulvermaling	Cable Panel
23130-628	RAL 7021	Struktur Pulvermaling	Cable Panel
23130-420	RAL 7021	Struktur Pulvermaling	Cable Panel
23130-150	RAL 7021	Struktur Pulvermaling	Cable Panel
23130-151	RAL 7021	Struktur Pulvermaling	Cable Panel
23130-421	RAL 7021	Struktur Pulvermaling	Cable Panel
23130-499	RAL 7021	Struktur Pulvermaling	Cable Panel

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Vores kraftfulde portefølje af mærker:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE