

Fan Control Module FCM3

Management Module for Fan Control and Voltage Monitoring.



ZERTIFIZIERUNGEN



MERKMALE

The fan control module (FCM3) is a standalone fan controller for 12 or 24 V fans

Up to 6 fans can be monitored and controlled

Signal monitoring of up to 6 temperature sensors

Monitoring of 3.3 V, 5 V, 12 / 24 V and -12 V voltages

FCM3 supply voltage: 12 to 24 V

Can control status LEDs for Over Temp, Fan Fail, 3.3 V, 5 V, 12 / 24 V and -12 V

In case of overheating or the failure of a fan, the other fans will be set to full speed

Status information can be queried via SMBus interface

Suitable for a 4 wire fan with PWM

SPEZIFIKATIONEN

Table 1/1

Katalognummer	Passt zu	Tiefe	Höhe	Anzahl Verpackungen	Breite
23207-170	CompactPCI-Systeme	119mm	15mm	1	49mm
23207-172	CompactPCI-Systeme	119mm	15mm	1	40mm

WARNUNG

nVent-Produkte müssen in Übereinstimmung mit den Produktinformationsblättern und dem Schulungsmaterial von nVent installiert und verwendet werden. Informationsblätter sind verfügbar unter www.nVent.com sowie bei Ihrem nVent-Kundendienstvertreter. Unsachgemäße Installation, Missbrauch, Fehlanwendung oder andere Handlungen im Widerspruch zu den Anweisungen und Warnungen von nVent können zu Fehlfunktionen, Anlagenschäden, schwerer Körperverletzung sowie zum Tod führen und/oder haben die Annullierung der Garantie zur Folge.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Unser starkes markenportfolio:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE