

Modulschiene, vorne, Typ R-KD, robust, kurze Lippe, 1000 mm

KATALOGNUMMER

34566-201



Combinations of horizontal rails and side panels

	"H" can be combined.		"H" combination not recommended	
Support H		-		side rail not supported
Support L		+	side rail H (possible) if the side panel is not attached	side rail for bending and twisting not supported
Support L		side rail H (not)	side rail H (possible)	-
Horizontal rail		-		-
		side panel		Flexion H
		Support L		Flexion L
		Support H		Support L

 side panel

Der robuste Modulschiementyp kann Stoß und Vibrationen von bis zu 25 g standhalten.

ZERTIFIZIERUNGEN



MERKMALE

Typ R-VT „Robuste“ Modulschiene mit 3-Loch-Befestigung für höhere Stabilität

Aluminiumprofil, Oberfläche eloxiert, Kontaktfläche leitfähig, ohne TE-Bedruckung

PRODUKTMERKMALE

Breite Gestell: 195HP

Anzahl Verpackungen: 1

Oberfläche: Eloxiert

Länge: 1000mm

Material: Aluminium

Produktfamilie: EuropacPRO

Produkttyp: Modulschiene

Typ: Robust, KD

Passt zu: Baugruppenträger

Net Weight: 0.6kg

ZUSÄTZLICHE PRODUKTDDETAILS

Ohne stirnseitiges M4 Gewinde, ohne Bedruckung und ohne Klinkung für 19-Zoll Winkel.

WARNUNG

nVent-Produkte müssen in Übereinstimmung mit den Produktinformationsblättern und dem Schulungsmaterial von nVent installiert und verwendet werden. Informationsblätter sind verfügbar unter www.nVent.com sowie bei Ihrem nVent-Kundendienstvertreter. Unsachgemäße Installation, Missbrauch, Fehlanwendung oder andere Handlungen im Widerspruch zu den Anweisungen und Warnungen von nVent können zu Fehlfunktionen, Anlagenschäden, schwerer Körperverletzung sowie zum Tod führen und/oder haben die Annullierung der Garantie zur Folge.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Unser starkes markenportfolio:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE