

# 19" Assembly Kit M6

## Data Solutions



For standard grounding use a grounding nut and washer on at least one attachment point.

When 19" assembly kit is used with conductive 19" panel mount, grounding cage nuts are not needed.

### CERTIFICATIONS



### FEATURES

Assembly kits for assembly of 19" components into a cabinet

For mounting of front panels, distribution fields or other components on the frame, slide mounts or depth members with square cut-outs

### SPECIFICATIONS

**Product Type:** Assembly Kit

**Finish:** Zinc Plated

Table 1/2

| Catalog Number | Length | Package Quantity | Thread Size | Material | Product Family | Type |
|----------------|--------|------------------|-------------|----------|----------------|------|
|----------------|--------|------------------|-------------|----------|----------------|------|

|           |      |     |    |            |   |                            |
|-----------|------|-----|----|------------|---|----------------------------|
| 21190-095 |      | 4   | M6 | Steel, ABS | RatiopacPRO,<br>RatiopacPRO<br>AIR,<br>CompacPRO,<br>PropacPRO,<br>Comptec, Inpac,<br>MultipacPRO,<br>Varistar CP,<br>Eurorack,<br>Outdoor              | Mounting Kit               |
| 21120-213 |      | 4   | M6 | Steel      |   | Mounting Kit               |
| 21120-196 | 16mm | 4   | M6 | Steel      |   | Mounting Kit,<br>Grounding |
| 21100-435 |      | 8   | M6 | Steel, ABS | RatiopacPRO,<br>RatiopacPRO<br>AIR,<br>CompacPRO,<br>PropacPRO,<br>Comptec, Inpac,<br>MultipacPRO,<br>Varistar CP,<br>Novastar,<br>Eurorack,<br>Outdoor | Mounting Kit               |
| 21120-199 | 13mm | 100 | M6 | Steel      |   | Mounting Kit,<br>Grounding |
| 21120-198 | 16mm | 50  | M6 | Steel      |   | Mounting Kit,<br>Grounding |
| 21120-197 | 16mm | 32  | M6 | Steel      |   | Mounting Kit,<br>Grounding |
| 21190-435 |      | 32  | M6 | Steel, ABS | RatiopacPRO,<br>RatiopacPRO<br>AIR,<br>CompacPRO,<br>PropacPRO,<br>Comptec, Inpac,<br>MultipacPRO,<br>Varistar CP,<br>Eurorack,<br>Outdoor              | Mounting Kit               |

|           |  |     |    |            |   |              |
|-----------|--|-----|----|------------|---|--------------|
| 21101-810 |  | 100 | M6 | Steel, ABS | RatiopacPRO,<br>RatiopacPRO<br>AIR,<br>CompacPRO,<br>PropacPRO,<br>Comptec, Inpac,<br>MultipacPRO,<br>Varistar CP,<br>Novastar,<br>Eurorack,<br>Outdoor | Mounting Kit |
| 21101-809 |  | 50  | M6 | Steel, ABS | RatiopacPRO,<br>RatiopacPRO<br>AIR,<br>CompacPRO,<br>PropacPRO,<br>Comptec, Inpac,<br>MultipacPRO,<br>Varistar CP,<br>Novastar,<br>Eurorack,<br>Outdoor | Mounting Kit |
| 21120-215 |  | 32  | M6 | Steel      |   | Mounting Kit |
| 21120-214 |  | 50  | M6 | Steel      |   | Mounting Kit |
| 21120-216 |  | 100 | M6 | Steel      |   | Mounting Kit |

Table 2/2

| Catalog Number | Works With  | Certifications |
|----------------|---|----------------|
| 21190-095      | 19" Cases, 19" Wallmount, 19" Indoor Cabinets, 19" Outdoor Cabinets | RoHS           |
| 21120-213      | Front Panels, Eurorack, Novastar, Varistar, Varistar CP             |                |
| 21120-196      | Front Panels, Eurorack, Novastar, Varistar, Varistar CP             |                |
| 21100-435      | 19" Cases, 19" Wallmount, 19" Indoor Cabinets, 19" Outdoor Cabinets | RoHS           |
| 21120-199      | Front Panels, Eurorack, Novastar, Varistar, Varistar CP             |                |
| 21120-198      | Front Panels, Eurorack, Novastar, Varistar, Varistar CP             |                |
| 21120-197      | Front Panels, Eurorack, Novastar, Varistar, Varistar CP             |                |
| 21190-435      | 19" Cases, 19" Wallmount, 19" Indoor Cabinets, 19" Outdoor Cabinets | RoHS           |
| 21101-810      | 19" Cases, 19" Wallmount, 19" Indoor Cabinets, 19" Outdoor Cabinets | RoHS           |

| Catalog Number | Works With  | Certifications |
|----------------|---|----------------|
| 21101-809      | 19" Cases, 19" Wallmount, 19" Indoor Cabinets, 19" Outdoor Cabinets | RoHS           |
| 21120-215      | Front Panels, Eurorack, Novastar, Varistar, Varistar CP             |                |
| 21120-214      | Front Panels, Eurorack, Novastar, Varistar, Varistar CP             |                |
| 21120-216      | Front Panels, Eurorack, Novastar, Varistar, Varistar CP             |                |

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**