


VPX Backplane

The nVent SCHROFF VPX Backplane have excellent Signal Integrity for highest data transfer rates.



CERTIFICERINGER



FUNKTIONER

In accordance with: VITA 46.0 VPX base standard; VITA 46.3 Serial RapidIO on VPX; VITA 46.4 PCI Express on VPX Fabric Connector; VITA 46.7 Ethernet on VPX Fabric Connector; VITA 46.11 System Management for VPX

DIP switch for system slot settings

JTAG connections

Lockable aux utility and sense connectors

M4 power studs for power supply, max. 22 A per slot for each voltage

SPECIFIKATIONER

Table 1/2

| Katalognummer | Product Type | Number of Slots | Rack Height | Backplane Type | Slot Width | Connector Type |
|---------------|--------------|-----------------|-------------|----------------|------------|----------------|
| 23001-834 | Backplane | 9 | 3U | VPX, VITA 65 | 5HP | MultiGig |
| 23001-816 | Backplane | 10 | 6U | VPX, VITA 65 | 5HP | MultiGig |
| 23001-815 | Backplane | 7 | 3U | VPX, VITA 65 | 5HP | MultiGig |
| 23001-814 | Backplane | 7 | 3U | VPX, VITA 65 | 5HP | MultiGig |
| 23001-812 | Backplane | 5 | 3U | VPX Full-mesh | 4HP | MultiGig |

| Katalognummer | Product Type | Number of Slots | Rack Height | Backplane Type | Slot Width | Connector Type |
|---------------|--------------|-----------------|-------------|----------------|------------|----------------|
| 23001-813 | Backplane | 5 | 3U | VPX Full-mesh | 4HP | MultiGig |

Table 2/2

| Katalognummer | Power Connector Type | Utility Connector Type | Bredde | Pakke mængde | Certificeringer |
|---------------|----------------------|------------------------|----------|--------------|-----------------|
| 23001-834 | Powerstuds M4 | Microfit, 8-pin | 253mm | 1 | VITA |
| 23001-816 | Powerstuds M4 | Microfit, 8-pin | 262.55mm | 1 | VITA, RoHS |
| 23001-815 | Powerstuds M4 | Microfit, 8-pin | 186.46mm | 1 | RoHS, VITA |
| 23001-814 | Powerstuds M4 | Microfit, 8-pin | 186.46mm | 1 | VITA, RoHS |
| 23001-812 | Powerstuds M4 | Microfit, 8-pin | 120.67mm | 1 | VITA, RoHS |
| 23001-813 | Powerstuds M4 | Microfit, 8-pin | 120.67mm | 1 | RoHS, VITA |

YDERLIGERE PRODUKTOPLYSNINGER

Other VPX Backplanes and custom VPX Backplane designs on request.

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden unndladelser af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Vores kraftfulde portefølje af mærker:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE