

Modulschiene, vorne, Typ R-KD, robust, kurzes Dach, 40 TE

KATALOGNUMMER

34566-240



Combinations of horizontal rails and side panels

	"H" can be combined.		"H" combination not recommended	
Support H		-		not recommended
Support H		+	not recommended	not recommended
Support H		+	not recommended	not recommended
Horizontal rail		+	+	+
Horizontal rail		+	+	+
Horizontal rail		+	+	+
Horizontal rail		+	+	+
Horizontal rail		+	+	+
Horizontal rail		+	+	+
Horizontal rail		+	+	+
Horizontal rail		+	+	+

Der robuste Modulschiementyp kann Stoß und Vibrationen von bis zu 25 g standhalten.

ZERTIFIZIERUNGEN



MERKMALE

Typ R-VT „Robuste“ Modulschiene mit 3-Loch-Befestigung für höhere Stabilität

Aluminiumprofil, Oberfläche eloxiert, Kontaktfläche leitfähig, ohne TE-Bedruckung

PRODUKTMERKMALE

Breite Gestell: 40HP

Anzahl Verpackungen: 1

Oberfläche: Eloxiert

Länge: 208.28mm

Material: Aluminium

Produktfamilie: EuropacPRO

Produkttyp: Modulschiene

Typ: Robust, KD

Passt zu: Baugruppenträger

Gross Weight: 0.118kg

ZUSÄTZLICHE PRODUKTDDETAILS

Ohne stirnseitiges M4 Gewinde, ohne Bedruckung und ohne Klinkung für 19-Zoll Winkel.

WARNUNG

nVent-Produkte müssen in Übereinstimmung mit den Produktinformationsblättern und dem Schulungsmaterial von nVent installiert und verwendet werden. Informationsblätter sind verfügbar unter www.nVent.com sowie bei Ihrem nVent-Kundendienstvertreter. Unsachgemäße Installation, Missbrauch, Fehlanwendung oder andere Handlungen im Widerspruch zu den Anweisungen und Warnungen von nVent können zu Fehlfunktionen, Anlagenschäden, schwerer Körperverletzung sowie zum Tod führen und/oder haben die Annullierung der Garantie zur Folge.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Unser starkes markenportfolio:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE