Transposition Sections Lay-in Hinged-Cover

Lay-in Hinged-Cover Transposition Sections are used when it is necessary to rotate the open side of the wireway run by 90 degrees and still retain the lay-in feature.

INDUSTRY STANDARDS

Certified by Canadian Standards Association.

FEATURES

Lay-in Hinged-Cover Transposition Sections are used when it is necessary to rotate the open side of the wireway run by 90 degrees and still retain the lay-in feature

SPECIFICATIONS

Color Code: ANSI 61

Finish: Galvanized; Powder Coated

Color: Gray

Material: Mild Steel

Table 1/1

Catalog Number	Article Number	Type	Height	Width	Thickness	Sealing Plate Quantity
F44LE9KOKT	19800	Transposition Section	102mm	102mm	1.9mm	1
F66LE9KT	19830	Transposition Section	152mm	152mm	1.9mm	1
F22LKT	19770	Transposition Section	64mm	64mm	1.9mm	1
F66LKOKT	19860	Transposition Section	152mm	152mm	1.9mm	1
F44LE9KT	19790	Transposition Section	102mm	102mm	1.9mm	1
F44LKOKT	19820	Transposition Section	102mm	102mm	1.9mm	1
F22LE9KOKT	19760	Transposition Section	64mm	64mm	1.9mm	1
F88LE9KOKT	19450	Transposition Section	203mm	203mm	1.9mm	1
F66LE9KOKT	19840	Transposition Section	152mm	152mm	1.9mm	1
F22LE9KT	19750	Transposition Section	64mm	64mm	1.9mm	1
F88LE9KT	19440	Transposition Section	203mm	203mm	1.9mm	1
F44LKT	19810	Transposition Section	102mm	102mm	1.9mm	1
F22LKOKT	19780	Transposition Section	64mm	64mm	1.9mm	1
F66LKT	19850	Transposition Section	152mm	152mm	1.9mm	1

ADDITIONAL PRODUCT DETAILS

Each sealing plate also includes one gasket and one set of screws to join sections.

Certified by Canadian Standards Association.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.