

# Varistar CP Side Panel, Screw-Fixed

Screw assembly side panel for Varistar CP cabinet.



## FEATURES

Screw fixed, Robust and Single person mountable Side Panel

Side panel without grounding kit

## SPECIFICATIONS

**Product Type:** Cabinet/Rack Panel

Table 1/5

| Catalog Number | Rack Height | Height | Depth  | Protection Rating | Package Quantity | Color      |
|----------------|-------------|--------|--------|-------------------|------------------|------------|
| 21630-266      | 29U         | 1400mm | 800mm  | IP20              | 2                | Black Grey |
| 21630-278      | 42U         | 2000mm | 600mm  | IP20              | 2                | Black Grey |
| 21630-231      | 33U         | 1600mm | 900mm  | IP55              | 2                | Black Grey |
| 21630-079      | 42U         | 2000mm | 1200mm | IP55              | 2                | Black Grey |
| 21630-238      | 42U         | 2000mm | 600mm  | IP55              | 2                | Black Grey |
| 21630-226      | 29U         | 1400mm | 800mm  | IP55              | 2                | Black Grey |
| 21630-271      | 33U         | 1600mm | 900mm  | IP20              | 2                | Black Grey |
| 21630-279      | 42U         | 2000mm | 800mm  | IP20              | 2                | Black Grey |
| 21630-228      | 29U         | 1400mm | 1000mm | IP55              | 2                | Black Grey |
| 21630-268      | 29U         | 1400mm | 1000mm | IP20              | 2                | Black Grey |
| 21630-239      | 42U         | 2000mm | 800mm  | IP55              | 2                | Black Grey |
| 21630-081      | 47U         | 2200mm | 1100mm | IP55              | 2                | Black Grey |

| Catalog Number | Rack Height | Height | Depth  | Protection Rating | Package Quantity | Color      |
|----------------|-------------|--------|--------|-------------------|------------------|------------|
| 21630-227      | 29U         | 1400mm | 900mm  | IP55              | 2                | Black Grey |
| 21630-272      | 33U         | 1600mm | 1000mm | IP20              | 2                | Black Grey |
| 21630-280      | 42U         | 2000mm | 900mm  | IP20              | 2                | Black Grey |
| 21630-267      | 29U         | 1400mm | 900mm  | IP20              | 2                | Black Grey |
| 21630-264      | 24U         | 1200mm | 1000mm | IP20              | 2                | Black Grey |
| 21630-082      | 47U         | 2200mm | 1200mm | IP55              | 2                | Black Grey |
| 21630-240      | 42U         | 2000mm | 900mm  | IP55              | 2                | Black Grey |
| 21630-224      | 24U         | 1200mm | 1000mm | IP55              | 2                | Black Grey |

Table 2/5

| Catalog Number | Rack Height | Height | Depth  | Protection Rating | Package Quantity | Color      |
|----------------|-------------|--------|--------|-------------------|------------------|------------|
| 21630-927      | 24U         | 1200mm | 900mm  | IP55              | 2                | Black Grey |
| 21630-225      | 29U         | 1400mm | 600mm  | IP55              | 2                | Black Grey |
| 21630-043      | 42U         | 2000mm | 1000mm | IP20              | 2                | Black Grey |
| 21630-223      | 24U         | 1200mm | 900mm  | IP55              | 2                | Black Grey |
| 21630-241      | 42U         | 2000mm | 1000mm | IP55              | 2                | Black Grey |
| 21630-263      | 24U         | 1200mm | 900mm  | IP20              | 2                | Black Grey |
| 21630-274      | 38U         | 1800mm | 800mm  | IP20              | 2                | Black Grey |
| 21630-270      | 33U         | 1600mm | 800mm  | IP20              | 2                | Black Grey |
| 21630-249      | 47U         | 2200mm | 1100mm | IP55              | 2                | Black Grey |
| 21630-047      | 47U         | 2200mm | 1100mm | IP20              | 2                | Black Grey |
| 21630-230      | 33U         | 1600mm | 800mm  | IP55              | 2                | Black Grey |
| 21630-048      | 47U         | 2200mm | 1200mm | IP20              | 2                | Black Grey |
| 21630-243      | 42U         | 2000mm | 1200mm | IP55              | 2                | Black Grey |
| 21630-273      | 38U         | 1800mm | 600mm  | IP20              | 2                | Black Grey |
| 21630-229      | 33U         | 1600mm | 600mm  | IP55              | 2                | Black Grey |
| 21630-045      | 42U         | 2000mm | 1200mm | IP20              | 2                | Black Grey |
| 21630-242      | 42U         | 2000mm | 1100mm | IP55              | 2                | Black Grey |
| 21630-233      | 38U         | 1800mm | 600mm  | IP55              | 2                | Black Grey |
| 21630-044      | 42U         | 2000mm | 1100mm | IP20              | 2                | Black Grey |
| 21630-467      | 29U         | 1400mm | 600mm  | IP55              | 2                | Black Grey |

Table 3/5

| Catalog Number | Rack Height | Height | Depth  | Protection Rating | Package Quantity | Color      |
|----------------|-------------|--------|--------|-------------------|------------------|------------|
| 21630-250      | 47U         | 2200mm | 1200mm | IP55              | 2                | Black Grey |
| 21630-236      | 38U         | 1800mm | 1000mm | IP55              | 2                | Black Grey |
| 21630-234      | 38U         | 1800mm | 800mm  | IP55              | 2                | Black Grey |
| 21630-276      | 38U         | 1800mm | 1000mm | IP20              | 2                | Black Grey |
| 21630-235      | 38U         | 1800mm | 900mm  | IP55              | 2                | Black Grey |
| 21630-269      | 33U         | 1600mm | 600mm  | IP20              | 2                | Black Grey |
| 21630-078      | 42U         | 2000mm | 1100mm | IP55              | 2                | Black Grey |
| 21630-277      | 42U         | 2000mm | 300mm  | IP20              | 2                | Black Grey |
| 21630-275      | 38U         | 1800mm | 900mm  | IP20              | 2                | Black Grey |
| 21630-237      | 42U         | 2000mm | 300mm  | IP55              | 2                | Black Grey |
| 21630-232      | 33U         | 1600mm | 1000mm | IP55              | 2                | Black Grey |
| 21630-262      | 24U         | 1200mm | 800mm  | IP20              | 2                | Black Grey |
| 21630-933      | 38U         | 1800mm | 900mm  | IP55              | 2                | Black Grey |
| 21630-283      | 47U         | 2200mm | 800mm  | IP20              | 2                | Black Grey |
| 21630-478      | 47U         | 2200mm | 600mm  | IP55              | 2                | Black Grey |
| 21630-465      | 24U         | 1200mm | 600mm  | IP55              | 2                | Black Grey |
| 21630-477      | 47U         | 2200mm | 300mm  | IP55              | 2                | Black Grey |
| 21630-246      | 47U         | 2200mm | 800mm  | IP55              | 2                | Black Grey |
| 21630-077      | 42U         | 2000mm | 1000mm | IP55              | 2                | Black Grey |
| 21630-284      | 47U         | 2200mm | 900mm  | IP20              | 2                | Black Grey |

Table 4/5

| Catalog Number | Rack Height | Height | Depth  | Protection Rating | Package Quantity | Color      |
|----------------|-------------|--------|--------|-------------------|------------------|------------|
| 21630-931      | 33U         | 1600mm | 900mm  | IP55              | 2                | Black Grey |
| 21630-476      | 42U         | 2000mm | 900mm  | IP55              | 2                | Black Grey |
| 21630-930      | 29U         | 1400mm | 1000mm | IP55              | 2                | Black Grey |
| 21630-475      | 42U         | 2000mm | 800mm  | IP55              | 2                | Black Grey |
| 21630-247      | 47U         | 2200mm | 900mm  | IP55              | 2                | Black Grey |
| 21630-471      | 38U         | 1800mm | 600mm  | IP55              | 2                | Black Grey |
| 21630-474      | 42U         | 2000mm | 600mm  | IP55              | 2                | Black Grey |
| 21630-046      | 47U         | 2200mm | 1000mm | IP20              | 2                | Black Grey |
| 21630-932      | 33U         | 1600mm | 1000mm | IP55              | 2                | Black Grey |
| 21630-473      | 42U         | 2000mm | 300mm  | IP55              | 2                | Black Grey |

| Catalog Number | Rack Height | Height | Depth  | Protection Rating | Package Quantity | Color      |
|----------------|-------------|--------|--------|-------------------|------------------|------------|
| 21630-248      | 47U         | 2200mm | 1000mm | IP55              | 2                | Black Grey |
| 21630-472      | 38U         | 1800mm | 800mm  | IP55              | 2                | Black Grey |
| 21630-221      | 24U         | 1200mm | 600mm  | IP55              | 2                | Black Grey |
| 21630-469      | 33U         | 1600mm | 600mm  | IP55              | 2                | Black Grey |
| 21630-928      | 24U         | 1200mm | 1000mm | IP55              | 2                | Black Grey |
| 21630-050      | 52U         | 2450mm | 1100mm | IP20              | 2                | Black Grey |
| 21630-468      | 29U         | 1400mm | 800mm  | IP55              | 2                | Black Grey |
| 21630-261      | 24U         | 1200mm | 600mm  | IP20              | 2                | Black Grey |
| 21630-265      | 29U         | 1400mm | 600mm  | IP20              | 2                | Black Grey |
| 21630-934      | 38U         | 1800mm | 1000mm | IP55              | 2                | Black Grey |

Table 5/5

| Catalog Number | Rack Height | Height | Depth  | Protection Rating | Package Quantity | Color      |
|----------------|-------------|--------|--------|-------------------|------------------|------------|
| 21630-281      | 47U         | 2200mm | 300mm  | IP20              | 2                | Black Grey |
| 21630-051      | 52U         | 2450mm | 1200mm | IP20              | 2                | Black Grey |
| 21630-244      | 47U         | 2200mm | 300mm  | IP55              | 2                | Black Grey |
| 21630-049      | 52U         | 2450mm | 1000mm | IP20              | 2                | Black Grey |
| 21630-222      | 24U         | 1200mm | 800mm  | IP55              | 2                | Black Grey |
| 21630-466      | 24U         | 1200mm | 800mm  | IP55              | 2                | Black Grey |
| 21630-080      | 47U         | 2200mm | 1000mm | IP55              | 2                | Black Grey |
| 21630-929      | 29U         | 1400mm | 900mm  | IP55              | 2                | Black Grey |
| 21630-282      | 47U         | 2200mm | 600mm  | IP20              | 2                | Black Grey |
| 21630-480      | 47U         | 2200mm | 900mm  | IP55              | 2                | Black Grey |
| 21630-245      | 47U         | 2200mm | 600mm  | IP55              | 2                | Black Grey |
| 21630-479      | 47U         | 2200mm | 800mm  | IP55              | 2                | Black Grey |
| 21630-470      | 33U         | 1600mm | 800mm  | IP55              | 2                | Black Grey |

Table 1/5

| Catalog Number | Color Code | Finish        | Material | Type                    |
|----------------|------------|---------------|----------|-------------------------|
| 21630-266      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |
| 21630-278      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |
| 21630-231      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |

| Catalog Number | Color Code | Finish        | Material | Type                    |
|----------------|------------|---------------|----------|-------------------------|
| 21630-079      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |
| 21630-238      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |
| 21630-226      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |
| 21630-271      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |
| 21630-279      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |
| 21630-228      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |
| 21630-268      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |
| 21630-239      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |
| 21630-081      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |
| 21630-227      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |
| 21630-272      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |
| 21630-280      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |
| 21630-267      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |
| 21630-264      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |
| 21630-082      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |
| 21630-240      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |
| 21630-224      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |

Table 2/5

| Catalog Number | Color Code | Finish        | Material | Type                    |
|----------------|------------|---------------|----------|-------------------------|
| 21630-927      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |
| 21630-225      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |

| Catalog Number | Color Code | Finish        | Material | Type                    |
|----------------|------------|---------------|----------|-------------------------|
| 21630-043      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |
| 21630-223      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |
| 21630-241      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |
| 21630-263      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |
| 21630-274      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |
| 21630-270      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |
| 21630-249      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |
| 21630-047      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |
| 21630-230      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |
| 21630-048      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |
| 21630-243      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |
| 21630-273      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |
| 21630-229      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |
| 21630-045      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |
| 21630-242      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |
| 21630-233      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |
| 21630-044      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |
| 21630-467      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |

Table 3/5

| Catalog Number | Color Code | Finish        | Material | Type                    |
|----------------|------------|---------------|----------|-------------------------|
| 21630-250      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |

| Catalog Number | Color Code | Finish        | Material | Type                    |
|----------------|------------|---------------|----------|-------------------------|
| 21630-236      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |
| 21630-234      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |
| 21630-276      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |
| 21630-235      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |
| 21630-269      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |
| 21630-078      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |
| 21630-277      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |
| 21630-275      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |
| 21630-237      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |
| 21630-232      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |
| 21630-262      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |
| 21630-933      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |
| 21630-283      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |
| 21630-478      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |
| 21630-465      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |
| 21630-477      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |
| 21630-246      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |
| 21630-077      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |
| 21630-284      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed |

Table 4/5

| Catalog Number | Color Code | Finish | Material | Type |
|----------------|------------|--------|----------|------|
|----------------|------------|--------|----------|------|

|           |          |               |       |                         |
|-----------|----------|---------------|-------|-------------------------|
| 21630-931 | RAL 7021 | Powder Coated | Steel | Side Panel, Screw Fixed |
| 21630-476 | RAL 7021 | Powder Coated | Steel | Side Panel, Screw Fixed |
| 21630-930 | RAL 7021 | Powder Coated | Steel | Side Panel, Screw Fixed |
| 21630-475 | RAL 7021 | Powder Coated | Steel | Side Panel, Screw Fixed |
| 21630-247 | RAL 7021 | Powder Coated | Steel | Side Panel, Screw Fixed |
| 21630-471 | RAL 7021 | Powder Coated | Steel | Side Panel, Screw Fixed |
| 21630-474 | RAL 7021 | Powder Coated | Steel | Side Panel, Screw Fixed |
| 21630-046 | RAL 7021 | Powder Coated | Steel | Side Panel, Screw Fixed |
| 21630-932 | RAL 7021 | Powder Coated | Steel | Side Panel, Screw Fixed |
| 21630-473 | RAL 7021 | Powder Coated | Steel | Side Panel, Screw Fixed |
| 21630-248 | RAL 7021 | Powder Coated | Steel | Side Panel, Screw Fixed |
| 21630-472 | RAL 7021 | Powder Coated | Steel | Side Panel, Screw Fixed |
| 21630-221 | RAL 7021 | Powder Coated | Steel | Side Panel, Screw Fixed |
| 21630-469 | RAL 7021 | Powder Coated | Steel | Side Panel, Screw Fixed |
| 21630-928 | RAL 7021 | Powder Coated | Steel | Side Panel, Screw Fixed |
| 21630-050 | RAL 7021 | Powder Coated | Steel | Side Panel, Screw Fixed |
| 21630-468 | RAL 7021 | Powder Coated | Steel | Side Panel, Screw Fixed |
| 21630-261 | RAL 7021 | Powder Coated | Steel | Side Panel, Screw Fixed |
| 21630-265 | RAL 7021 | Powder Coated | Steel | Side Panel, Screw Fixed |
| 21630-934 | RAL 7021 | Powder Coated | Steel | Side Panel, Screw Fixed |

Table 5/5

| Catalog Number | Color Code | Finish | Material | Type |
|----------------|------------|--------|----------|------|
|----------------|------------|--------|----------|------|

|           |          |               |       |                         |
|-----------|----------|---------------|-------|-------------------------|
| 21630-281 | RAL 7021 | Powder Coated | Steel | Side Panel, Screw Fixed |
| 21630-051 | RAL 7021 | Powder Coated | Steel | Side Panel, Screw Fixed |
| 21630-244 | RAL 7021 | Powder Coated | Steel | Side Panel, Screw Fixed |
| 21630-049 | RAL 7021 | Powder Coated | Steel | Side Panel, Screw Fixed |
| 21630-222 | RAL 7021 | Powder Coated | Steel | Side Panel, Screw Fixed |
| 21630-466 | RAL 7021 | Powder Coated | Steel | Side Panel, Screw Fixed |
| 21630-080 | RAL 7021 | Powder Coated | Steel | Side Panel, Screw Fixed |
| 21630-929 | RAL 7021 | Powder Coated | Steel | Side Panel, Screw Fixed |
| 21630-282 | RAL 7021 | Powder Coated | Steel | Side Panel, Screw Fixed |
| 21630-480 | RAL 7021 | Powder Coated | Steel | Side Panel, Screw Fixed |
| 21630-245 | RAL 7021 | Powder Coated | Steel | Side Panel, Screw Fixed |
| 21630-479 | RAL 7021 | Powder Coated | Steel | Side Panel, Screw Fixed |
| 21630-470 | RAL 7021 | Powder Coated | Steel | Side Panel, Screw Fixed |

## ADDITIONAL PRODUCT DETAILS

---

Please purchase the grounding kit separately.

## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

All locations

+1.763.422.2661

Chat with us:

[nvent.com/schroff](https://nvent.com/schroff)

### Europe

Straubenhardt, Germany

+49.7082.794.0

Betschdorf, France

+33.3.88.90.64.90

Warsaw, Poland

+48.22.209.98.35

Assago, Italy

+39.02.932.7141

Chat with us:

[nvent.com/schroff](https://nvent.com/schroff)

### Asia

Shanghai, China

+86.21.2412.6943

Qingdao, China

+86.532.8771.6101

Singapore

+65.6768.5800

Shin-Yokohama, Japan

+81.45.476.0271

Chat with us:

[nvent.com/schroff](https://nvent.com/schroff)

### Middle East & India

Dubai, United Arab

Emirates

+971.4.378.1700

Bangalore, India

+91.80.6715.2001

Istanbul, Turkey

+90.216.250.7374

Chat with us:

[nvent.com/schroff](https://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY**

**ERICO**

**HOFFMAN**

**ILSCO**

**SCHROFF**

**TRACHTE**