

Interscale Mounting Plate for PCBs

Interscale mounting plate for the fixation of PCBs in small form factor desktop cases and 19" chassis.



FEATURES

Mounting plate (raised 4 mm) with integrated fan holder including fan kit for perforated case versions

Fans are simple to fit to the mounting plate using vibrationdamping fixing material

Does not fit for Interscale M for embedded NUC and 19"

SPECIFICATIONS

| | |
|------------------------|-------------------------|
| Finish: | Aluminum-Zinc Plated |
| Product Family: | Interscale |
| Product Type: | Mounting Plate |
| Type: | Mounting Plate |
| Works With: | Small Form Factor Cases |
| Material: | Steel |

Table 1/1

| Catalog Number | Width | Depth | Package Quantity | Height |
|----------------|-------|-------|------------------|--------|
| 24822-095 | 399mm | 221mm | 1 | 1mm |
| 24822-033 | 133mm | 133mm | 1 | 1mm |
| 24822-005 | 444mm | 221mm | 1 | 1mm |
| 24822-054 | 221mm | 177mm | 1 | 1mm |
| 24822-075 | 310mm | 221mm | 1 | 1mm |
| 24822-007 | 444mm | 310mm | 1 | 1mm |
| 24822-055 | 221mm | 221mm | 1 | 1mm |
| 24822-097 | 399mm | 310mm | 1 | 1mm |

| Catalog Number | Width | Depth | Package Quantity | Height |
|----------------|-------|-------|------------------|--------|
| 24822-034 | 133mm | 177mm | 1 | 1mm |

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE