

# Cable Runway Wall Angle Support

## Data Solutions



The Cable Runway Wall Angle Support provides support to ladder rack from a wall or other flat surface. It is made of 2-inch x 2-inch, 10ga painted or plated steel. The kit includes two J-bolts, nuts and screws.

### FEATURES

The Cable Runway Wall Angle Support provides support to ladder rack from a wall or other flat surface

It is made of 2-inch x 2-inch, 10ga painted or plated steel

The kit includes two J-bolts, nuts and screws

### SPECIFICATIONS

Table 1/1

| Catalog Number | Article Number | Material   | Finish        | Color     | Color Code | Thickness |
|----------------|----------------|------------|---------------|-----------|------------|-----------|
| LWASK15BLK     | 30001          | Mild Steel | Powder Coated | Jet Black | RAL 9005   | 3.04mm    |
| LWASK12W       | 29965          | Mild Steel | Powder Coated | White     |            | 3.04mm    |
| LWASK18W       | 29966          | Mild Steel | Powder Coated | White     |            | 3.04mm    |
| LWASK24BLK     | 17346          | Mild Steel | Powder Coated | Jet Black | RAL 9005   | 3.04mm    |
| LWASK24W       | 29967          | Mild Steel | Powder Coated | White     |            | 3.04mm    |
| LWASK12GZ      | 10122          | Mild Steel | Zinc Plated   |           |            | 3.04mm    |
| LWASK18GZ      | 10125          | Mild Steel | Zinc Plated   |           |            | 3.04mm    |
| LWASK6BLK      | 10115          | Mild Steel | Powder Coated | Jet Black | RAL 9005   | 3.04mm    |
| LWASK12G       | 10117          | Mild Steel | Powder Coated | Gray      | ANSI 61    | 3.04mm    |
| LWASK18G       | 10123          | Mild Steel | Powder Coated | Gray      | ANSI 61    | 3.04mm    |
| LWASK12BLK     | 10118          | Mild Steel | Powder Coated | Jet Black | RAL 9005   | 3.04mm    |

| Catalog Number | Article Number | Material   | Finish        | Color     | Color Code | Thickness |
|----------------|----------------|------------|---------------|-----------|------------|-----------|
| LWASK15W       | 30002          | Mild Steel | Powder Coated | White     |            | 3.04mm    |
| LWASK6G        | 10114          | Mild Steel | Powder Coated | Gray      | ANSI 61    | 3.04mm    |
| LWASK18BLK     | 10124          | Mild Steel | Powder Coated | Jet Black | RAL 9005   | 3.04mm    |
| LWASK6GZ       | 10116          | Mild Steel | Zinc Plated   |           |            | 3.04mm    |

## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**