

# Varistar CP Frame



Varistar CP welded frame is available for static load requirements and can be integrated with 19", ETSI or mounting plate. Additionally, castors can be added to the frame if needed.

However, if you require castors for your application, you might want to consider a mobile frame that already includes castors.

## FEATURES

Welded, finish powder-coated, black gray, RAL 7021

St, 1.5 mm, zinc-plated, with central GND/grounding point

Static load-carrying capacity max. 1600 kg

Please order adjustable feet separately

## SPECIFICATIONS

- Static Load:** 1600kg
- Product Type:** Cabinet/Rack Frame
- Material:** Steel

Table 1/4

| Catalog Number | Rack Height | Height | Width | Depth  | Package Quantity | Color      |
|----------------|-------------|--------|-------|--------|------------------|------------|
| 20630-118      | 47U         | 2200mm | 800mm | 800mm  | 1                | Black Grey |
| 20630-067      | 24U         | 1200mm | 600mm | 900mm  | 1                | Black Grey |
| 20630-091      | 38U         | 1800mm | 600mm | 600mm  | 1                | Black Grey |
| 20630-120      | 47U         | 2200mm | 800mm | 1000mm | 1                | Black Grey |
| 20630-084      | 33U         | 1600mm | 600mm | 800mm  | 1                | Black Grey |
| 20630-126      | 52U         | 2450mm | 800mm | 1000mm | 1                | Black Grey |
| 20630-092      | 38U         | 1800mm | 600mm | 800mm  | 1                | Black Grey |
| 20630-119      | 47U         | 2200mm | 800mm | 900mm  | 1                | Black Grey |
| 20630-125      | 52U         | 2450mm | 600mm | 1200mm | 1                | Black Grey |

| Catalog Number | Rack Height | Height | Width | Depth  | Package Quantity | Color      |
|----------------|-------------|--------|-------|--------|------------------|------------|
| 20630-075      | 29U         | 1400mm | 600mm | 600mm  | 1                | Black Grey |
| 20630-089      | 33U         | 1600mm | 800mm | 900mm  | 1                | Black Grey |
| 20630-072      | 24U         | 1200mm | 800mm | 800mm  | 1                | Black Grey |
| 20630-117      | 47U         | 2200mm | 800mm | 600mm  | 1                | Black Grey |
| 20630-095      | 38U         | 1800mm | 800mm | 600mm  | 1                | Black Grey |
| 20630-128      | 52U         | 2450mm | 800mm | 1200mm | 1                | Black Grey |
| 20630-114      | 47U         | 2200mm | 600mm | 1000mm | 1                | Black Grey |
| 20630-096      | 38U         | 1800mm | 800mm | 800mm  | 1                | Black Grey |
| 20630-124      | 52U         | 2450mm | 600mm | 1100mm | 1                | Black Grey |
| 20630-079      | 29U         | 1400mm | 800mm | 600mm  | 1                | Black Grey |
| 20630-093      | 38U         | 1800mm | 600mm | 900mm  | 1                | Black Grey |

Table 2/4

| Catalog Number | Rack Height | Height | Width | Depth  | Package Quantity | Color      |
|----------------|-------------|--------|-------|--------|------------------|------------|
| 20630-087      | 33U         | 1600mm | 800mm | 600mm  | 1                | Black Grey |
| 20630-074      | 24U         | 1200mm | 800mm | 1000mm | 1                | Black Grey |
| 20630-094      | 38U         | 1800mm | 600mm | 1000mm | 1                | Black Grey |
| 20630-077      | 29U         | 1400mm | 600mm | 900mm  | 1                | Black Grey |
| 20630-073      | 24U         | 1200mm | 800mm | 900mm  | 1                | Black Grey |
| 20630-076      | 29U         | 1400mm | 600mm | 800mm  | 1                | Black Grey |
| 20630-122      | 47U         | 2200mm | 800mm | 1200mm | 1                | Black Grey |
| 20630-101      | 42U         | 2000mm | 600mm | 900mm  | 1                | Black Grey |
| 20630-097      | 38U         | 1800mm | 800mm | 900mm  | 1                | Black Grey |
| 20630-090      | 33U         | 1600mm | 800mm | 1000mm | 1                | Black Grey |
| 20630-088      | 33U         | 1600mm | 800mm | 800mm  | 1                | Black Grey |
| 20630-098      | 38U         | 1800mm | 800mm | 1000mm | 1                | Black Grey |
| 20630-068      | 24U         | 1200mm | 600mm | 1000mm | 1                | Black Grey |
| 20630-078      | 29U         | 1400mm | 600mm | 1000mm | 1                | Black Grey |
| 20630-123      | 52U         | 2450mm | 600mm | 1000mm | 1                | Black Grey |
| 20630-112      | 47U         | 2200mm | 600mm | 800mm  | 1                | Black Grey |
| 20630-102      | 42U         | 2000mm | 600mm | 1000mm | 1                | Black Grey |
| 20630-085      | 33U         | 1600mm | 600mm | 900mm  | 1                | Black Grey |
| 20630-065      | 24U         | 1200mm | 600mm | 600mm  | 1                | Black Grey |

| Catalog Number | Rack Height | Height | Width | Depth  | Package Quantity | Color      |
|----------------|-------------|--------|-------|--------|------------------|------------|
| 20630-110      | 42U         | 2000mm | 800mm | 1200mm | 1                | Black Grey |

Table 3/4

| Catalog Number | Rack Height | Height | Width | Depth  | Package Quantity | Color      |
|----------------|-------------|--------|-------|--------|------------------|------------|
| 20630-083      | 33U         | 1600mm | 600mm | 600mm  | 1                | Black Grey |
| 20630-105      | 42U         | 2000mm | 800mm | 600mm  | 1                | Black Grey |
| 20630-109      | 42U         | 2000mm | 800mm | 1100mm | 1                | Black Grey |
| 20630-082      | 29U         | 1400mm | 800mm | 1000mm | 1                | Black Grey |
| 20630-106      | 42U         | 2000mm | 800mm | 800mm  | 1                | Black Grey |
| 20630-100      | 42U         | 2000mm | 600mm | 800mm  | 1                | Black Grey |
| 20630-086      | 33U         | 1600mm | 600mm | 1000mm | 1                | Black Grey |
| 20630-107      | 42U         | 2000mm | 800mm | 900mm  | 1                | Black Grey |
| 20630-066      | 24U         | 1200mm | 600mm | 800mm  | 1                | Black Grey |
| 20630-104      | 42U         | 2000mm | 600mm | 1200mm | 1                | Black Grey |
| 20630-080      | 29U         | 1400mm | 800mm | 800mm  | 1                | Black Grey |
| 20630-108      | 42U         | 2000mm | 800mm | 1000mm | 1                | Black Grey |
| 20630-081      | 29U         | 1400mm | 800mm | 900mm  | 1                | Black Grey |
| 20630-127      | 52U         | 2450mm | 800mm | 1100mm | 1                | Black Grey |
| 20630-071      | 24U         | 1200mm | 800mm | 600mm  | 1                | Black Grey |
| 20630-261      | 42U         | 2000mm | 600mm | 300mm  | 1                | Black Grey |
| 20630-111      | 47U         | 2200mm | 600mm | 600mm  | 1                | Black Grey |
| 20630-115      | 47U         | 2200mm | 600mm | 1100mm | 1                | Black Grey |
| 20630-113      | 47U         | 2200mm | 600mm | 900mm  | 1                | Black Grey |
| 20630-121      | 47U         | 2200mm | 800mm | 1100mm | 1                | Black Grey |

Table 4/4

| Catalog Number | Rack Height | Height | Width | Depth  | Package Quantity | Color      |
|----------------|-------------|--------|-------|--------|------------------|------------|
| 20630-262      | 47U         | 2200mm | 600mm | 300mm  | 1                | Black Grey |
| 20630-116      | 47U         | 2200mm | 600mm | 1200mm | 1                | Black Grey |
| 20630-103      | 42U         | 2000mm | 600mm | 1100mm | 1                | Black Grey |
| 20630-099      | 42U         | 2000mm | 600mm | 600mm  | 1                | Black Grey |

Table 1/4

| Catalog Number | Color Code | Complies With | Frame Material | Type | Works With |
|----------------|------------|---------------|----------------|------|------------|
|----------------|------------|---------------|----------------|------|------------|

|           |          |                          |       |          |             |
|-----------|----------|--------------------------|-------|----------|-------------|
| 20630-118 | RAL 7021 |                          | Steel | Standard | Varistar CP |
| 20630-067 | RAL 7021 |                          | Steel | Standard | Varistar CP |
| 20630-091 | RAL 7021 |                          | Steel | Standard | Varistar CP |
| 20630-120 | RAL 7021 | IEC 61587-1, IEC 61587-3 | Steel | Standard | Varistar CP |
| 20630-084 | RAL 7021 |                          | Steel | Standard | Varistar CP |
| 20630-126 | RAL 7021 | IEC 61587-1, IEC 61587-3 | Steel | Standard | Varistar CP |
| 20630-092 | RAL 7021 |                          | Steel | Standard | Varistar CP |
| 20630-119 | RAL 7021 |                          | Steel | Standard | Varistar CP |
| 20630-125 | RAL 7021 | IEC 61587-1, IEC 61587-3 | Steel | Standard | Varistar CP |
| 20630-075 | RAL 7021 |                          | Steel | Standard | Varistar CP |
| 20630-089 | RAL 7021 |                          | Steel | Standard | Varistar CP |
| 20630-072 | RAL 7021 |                          | Steel | Standard | Varistar CP |
| 20630-117 | RAL 7021 |                          | Steel | Standard | Varistar CP |
| 20630-095 | RAL 7021 |                          | Steel | Standard | Varistar CP |
| 20630-128 | RAL 7021 | IEC 61587-1, IEC 61587-3 | Steel | Standard | Varistar CP |
| 20630-114 | RAL 7021 | IEC 61587-1, IEC 61587-3 | Steel | Standard | Varistar CP |
| 20630-096 | RAL 7021 |                          | Steel | Standard | Varistar CP |
| 20630-124 | RAL 7021 | IEC 61587-1, IEC 61587-3 | Steel | Standard | Varistar CP |
| 20630-079 | RAL 7021 |                          | Steel | Standard | Varistar CP |
| 20630-093 | RAL 7021 |                          | Steel | Standard | Varistar CP |

Table 2/4

| Catalog Number | Color Code | Complies With            | Frame Material | Type     | Works With  |
|----------------|------------|--------------------------|----------------|----------|-------------|
| 20630-087      | RAL 7021   |                          | Steel          | Standard | Varistar CP |
| 20630-074      | RAL 7021   |                          | Steel          | Standard | Varistar CP |
| 20630-094      | RAL 7021   |                          | Steel          | Standard | Varistar CP |
| 20630-077      | RAL 7021   |                          | Steel          | Standard | Varistar CP |
| 20630-073      | RAL 7021   |                          | Steel          | Standard | Varistar CP |
| 20630-076      | RAL 7021   |                          | Steel          | Standard | Varistar CP |
| 20630-122      | RAL 7021   | IEC 61587-1, IEC 61587-3 | Steel          | Standard | Varistar CP |
| 20630-101      | RAL 7021   |                          | Steel          | Standard | Varistar CP |

| Catalog Number | Color Code | Complies With            | Frame Material | Type     | Works With  |
|----------------|------------|--------------------------|----------------|----------|-------------|
| 20630-097      | RAL 7021   |                          | Steel          | Standard | Varistar CP |
| 20630-090      | RAL 7021   |                          | Steel          | Standard | Varistar CP |
| 20630-088      | RAL 7021   |                          | Steel          | Standard | Varistar CP |
| 20630-098      | RAL 7021   |                          | Steel          | Standard | Varistar CP |
| 20630-068      | RAL 7021   |                          | Steel          | Standard | Varistar CP |
| 20630-078      | RAL 7021   |                          | Steel          | Standard | Varistar CP |
| 20630-123      | RAL 7021   | IEC 61587-1, IEC 61587-3 | Steel          | Standard | Varistar CP |
| 20630-112      | RAL 7021   |                          | Steel          | Standard | Varistar CP |
| 20630-102      | RAL 7021   | IEC 61587-1, IEC 61587-3 | Steel          | Standard | Varistar CP |
| 20630-085      | RAL 7021   |                          | Steel          | Standard | Varistar CP |
| 20630-065      | RAL 7021   |                          | Steel          | Standard | Varistar CP |
| 20630-110      | RAL 7021   | IEC 61587-1, IEC 61587-3 | Steel          | Standard | Varistar CP |

Table 3/4

| Catalog Number | Color Code | Complies With            | Frame Material | Type     | Works With  |
|----------------|------------|--------------------------|----------------|----------|-------------|
| 20630-083      | RAL 7021   |                          | Steel          | Standard | Varistar CP |
| 20630-105      | RAL 7021   |                          | Steel          | Standard | Varistar CP |
| 20630-109      | RAL 7021   | IEC 61587-1, IEC 61587-3 | Steel          | Standard | Varistar CP |
| 20630-082      | RAL 7021   |                          | Steel          | Standard | Varistar CP |
| 20630-106      | RAL 7021   |                          | Steel          | Standard | Varistar CP |
| 20630-100      | RAL 7021   |                          | Steel          | Standard | Varistar CP |
| 20630-086      | RAL 7021   |                          | Steel          | Standard | Varistar CP |
| 20630-107      | RAL 7021   |                          | Steel          | Standard | Varistar CP |
| 20630-066      | RAL 7021   |                          | Steel          | Standard | Varistar CP |
| 20630-104      | RAL 7021   | IEC 61587-1, IEC 61587-3 | Steel          | Standard | Varistar CP |
| 20630-080      | RAL 7021   |                          | Steel          | Standard | Varistar CP |
| 20630-108      | RAL 7021   | IEC 61587-1, IEC 61587-3 | Steel          | Standard | Varistar CP |
| 20630-081      | RAL 7021   |                          | Steel          | Standard | Varistar CP |
| 20630-127      | RAL 7021   | IEC 61587-1, IEC 61587-3 | Steel          | Standard | Varistar CP |
| 20630-071      | RAL 7021   |                          | Steel          | Standard | Varistar CP |

| Catalog Number | Color Code | Complies With            | Frame Material | Type     | Works With  |
|----------------|------------|--------------------------|----------------|----------|-------------|
| 20630-261      | RAL 7021   |                          | Steel          | Standard | Varistar CP |
| 20630-111      | RAL 7021   |                          | Steel          | Standard | Varistar CP |
| 20630-115      | RAL 7021   | IEC 61587-1, IEC 61587-3 | Steel          | Standard | Varistar CP |
| 20630-113      | RAL 7021   |                          | Steel          | Standard | Varistar CP |
| 20630-121      | RAL 7021   | IEC 61587-1, IEC 61587-3 | Steel          | Standard | Varistar CP |

Table 4/4

| Catalog Number | Color Code | Complies With            | Frame Material | Type     | Works With  |
|----------------|------------|--------------------------|----------------|----------|-------------|
| 20630-262      | RAL 7021   |                          | Steel          | Standard | Varistar CP |
| 20630-116      | RAL 7021   | IEC 61587-1, IEC 61587-3 | Steel          | Standard | Varistar CP |
| 20630-103      | RAL 7021   | IEC 61587-1, IEC 61587-3 | Steel          | Standard | Varistar CP |
| 20630-099      | RAL 7021   |                          | Steel          | Standard | Varistar CP |

## ADDITIONAL PRODUCT DETAILS

Castor can be added to the frame. If you will need a castor for your application, you can order a mobile frame which include castors.

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**