

19" Front Panel, Plastic



19" plastic made clip on Front Panels with esthetic design are specially made for the datacom vertical. The easy clip on panels help in air flow management and also simultaneously providing an appealing look for the network rack.

CERTIFICATIONS



FEATURES

Attractive design

Simple fitting by clipping onto the 19" plane

SPECIFICATIONS

Accessory Type: Front panel

| Table 1/3 | | | | | | |
|----------------|-----------------|------------|---------------|----------|--------------|-------------|
| Catalog Number | Type | Mounting | EMC Shielding | Material | Front Finish | Rear Finish |
| 87927-991 | 19" Front Panel | Snapped in | No | ABS | Raw | Raw |
| 87927-992 | 19" Front Panel | Snapped in | No | ABS | Raw | Raw |
| 23130-623 | 19" Front Panel | Snapped in | No | ABS | | |
| 23130-622 | 19" Front Panel | Snapped in | No | ABS | | |

| Table 2/3 | | | | | | |
|----------------|------------|-------------|--------|------------|-------|-------|
| Catalog Number | Color Code | Rack Height | Height | Rack Width | Width | Depth |
| | | | | | | |

| | | | | | | |
|-----------|----------|----|---------|------|-------|------|
| 87927-991 | RAL 7035 | 1U | 43.71mm | 95HP | 482mm | 12mm |
| 87927-992 | RAL 7035 | 2U | 88.17mm | 95HP | 482mm | 12mm |
| 23130-623 | RAL 7035 | 6U | 266.6mm | 95HP | 483mm | 2mm |
| 23130-622 | RAL 9005 | 6U | 266.6mm | 95HP | 483mm | 2mm |

Table 3/3

| Catalog Number | Package Quantity |
|----------------|------------------|
| 87927-991 | 10 |
| 87927-992 | 10 |
| 23130-623 | 10 |
| 23130-622 | 10 |

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE