

# Pipe/Cable Clamp



## FEATURES

Captive threaded stud minimizes the need for additional hardware

With the UNICBAND Sign Support Bracket and Fixoband Strap, attachments to pipe and pole can be made

## SPECIFICATIONS

Table 1/2

Catalog Number	Article Number	Material	Finish	NB/DN	Outer Diameter (OD)	Width (W)
CR037HD	336300	Steel	Hot-Dip Galvanized	10	16 - 20 mm	16 mm
CR050HD	336310	Steel	Hot-Dip Galvanized	15	20 - 25 mm	16 mm
CR087S4	336422	Stainless Steel 304 (EN 1.4301)			32 - 34 mm	16 mm
CR075HD	336320	Steel	Hot-Dip Galvanized	20	26.9 - 31.8 mm	16 mm
CR087HD	336322	Steel	Hot-Dip Galvanized		32 - 34 mm	16 mm
CR200HD	336360	Steel	Hot-Dip Galvanized	50	59.2 - 63.5 mm	20 mm
CR100S4	336430	Stainless Steel 304 (EN 1.4301)		25	33.7 - 38 mm	20 mm

CatalogNumber	Article Number	Material	Finish	NB/DN	Outer Diameter (OD)	Width (W)
CR150HD	336350	Steel	Hot-Dip Galvanized	40	47 - 51 mm	20 mm
CR100HD	336330	Steel	Hot-Dip Galvanized	25	33.7 - 38 mm	20 mm
CR125HD	336340	Steel	Hot-Dip Galvanized	32	40.0 - 44.5 mm	20 mm

Table 2/2

Catalog Number	Article Number	Static Load 1 (F1)	Static Load 2 (F2)
CR037HD	336300	125N	550N
CR050HD	336310	125N	550N
CR087S4	336422	125N	550N
CR075HD	336320	125N	550N
CR087HD	336322	125N	550N
CR200HD	336360	250N	550N
CR100S4	336430	250N	550N
CR150HD	336350	250N	550N
CR100HD	336330	250N	550N
CR125HD	336340	250N	550N

## DIAGRAMS



## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

**North America**

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

**Europe**

Netherlands:

+31 800-0200135

France:

+33 800 901 793

**Europe**

Germany:

800 1890272

Other Countries:

+31 13 5835404

**APAC**

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**

