We connect and protect

# Intelligent iPDU, EN5337, 230 VAC, 1-PH, 32 A

## Data Solutions

### CATALOG NUMBER

**EN5337**

Modular, compact intelligent PDU with inlet metering. Ultra-Low Profile Design

### FEATURES

| |
|---|
| Enlogic EN5xxx Intelligent Power Distribution Units monitors input power of the entire PDU and individual outlet monitoring, provides billing grade unit level monitoring |
| High Visibility Data Display and Interactive Graphic Display |
| Measure circuit breaker loads across redundant feeds to avoid accidental downtime |
| Enables smart load balancing for power efficiency and maximized capacity utilization |
| Gigabit Ethernet Interface and redundant Ethernet (10/100) |
| iPDU DC power redundancy solution for up to 64 PDU's |
| Toolless Hot-Swap Controller |
| Input voltage 230 VAC, 1-phase |
| C13, C19 outlets |

### PRODUCT ATTRIBUTES

| |
|---|
| Product Family: Enlogic |
| Type: Intelligent PDU |
| Product Type: Socket Strip |

Socket Type: (38) C13; (6) C19

Socket Quantity: 44

Color: Black

Circuit Breaker: 16 A, 1-pole, Hy-Mag

Switched Outlets: No

Circuit Breaker Quantity: 2

Current Rating: 32A

Input Cable Location: Top Feed

Input Voltage: 200 – 240V

Phase: 1 PH

Interrupt Rating: 5kAIC

Max Power Input: 7.44 kVA

Output Voltage: 200 – 240VAC

Amperage (Derated Amperage): 32 A

Plug Type: IEC 60309 332P6 (IP44)

Rack Units: 0U

Removable Input Cable: No

Metering Type: Outlet

Package Quantity: 1

## ADDITIONAL PRODUCT DETAILS

Please order bracket for vertical mounting separately.

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.