

# Interscale Desktop Case, Perforated



Flexible desktop case with integrated EMC protection and perforated sides. Based on the nVent SCHROFF Interscale platform and developed in accordance with IEC 60297-3-109.

## CERTIFICATIONS



## FEATURES

Modular desktop case consisting of 4 assembled parts

Developed according to IEC 60297-3-109 (under progress at IEC)

Integrated EMC protection

Ingress protection up to IP 20

Color RAL 7016

Modified or customized cases upon request

## SPECIFICATIONS

<b>Material:</b>	Aluminum; Steel
<b>Type:</b>	Desktop
<b>Product Family:</b>	Interscale
<b>Protection Rating:</b>	IP20
<b>Color Code:</b>	RAL 7016
<b>Product Type:</b>	Small Form Factor Case

Table 1/1

Catalog Number	Package Quantity	Cooling	Color	Finish
----------------	------------------	---------	-------	--------

14825-154	1	Perforated	Anthracite Grey	Aluminum-Zinc Plated, Powder Coated
14825-254	1	Perforated	Anthracite Grey	Aluminum-Zinc Plated, Powder Coated
14825-255	1	Perforated	Anthracite Grey	Aluminum-Zinc Plated, Powder Coated
14825-197	1	Perforated	Anthracite Grey	Aluminum-Zinc Plated, Powder Coated
14825-275	1	Perforated	Anthracite Grey	Aluminum-Zinc Plated, Powder Coated
14825-195	1	Perforated	Anthracite Grey	Aluminum-Zinc Plated, Powder Coated
14825-295	1	Perforated	Anthracite Grey	Aluminum-Zinc Plated, Powder Coated
14825-297	1	Perforated	Anthracite Grey	Aluminum-Zinc Plated, Powder Coated
14825-175	1	Perforated	Anthracite Grey	Aluminum-Zinc Plated, Powder Coated
14825-375	1	Perforated	Anthracite Grey	Aluminum-Zinc Plated, Powder Coated
14825-395	1	Perforated	Anthracite Grey	Aluminum-Zinc Plated, Powder Coated
14825-155	1	Perforated	Anthracite Grey	Aluminum-Zinc Plated, Powder Coated
14825-397	1	Perforated	Anthracite Grey	Aluminum-Zinc Plated, Powder Coated

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

All locations

+1.763.422.2661

Chat with us:

[nvent.com/schroff](https://nvent.com/schroff)

### Europe

Straubenhardt, Germany

+49.7082.794.0

Betschdorf, France

+33.3.88.90.64.90

Warsaw, Poland

+48.22.209.98.35

Assago, Italy

+39.02.932.7141

Chat with us:

[nvent.com/schroff](https://nvent.com/schroff)

### Asia

Shanghai, China

+86.21.2412.6943

Qingdao, China

+86.532.8771.6101

Singapore

+65.6768.5800

Shin-Yokohama, Japan

+81.45.476.0271

Chat with us:

[nvent.com/schroff](https://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates

+971.4.378.1700

Bangalore, India

+91.80.6715.2001

Istanbul, Turkey

+90.216.250.7374

Chat with us:

[nvent.com/schroff](https://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY**

**ERICO**

**HOFFMAN**

**ILSCO**

**SCHROFF**

**TRACHTE**