

# Interscale Flexible Heat Conductor (FHC), 20 mm

## NÚMERO DE CATÁLOGO

**24830-005**



Conductor block expands/contracts vertically to compensate for tolerance stack up and optimizes surface contact and pressure along the thermal path; eliminates the need for a thermal gap pad.

## CERTIFICATIONS



## CARACTERÍSTICAS

Designed for Intel, AMD, Via, Freescale, NVidia and Texas Instrument processors that employ a BGA socket

Provides industry-leading conduction cooling performance, 10% improvement over current conduction cooling methods

Patent pending conduction cooling solution for small form factor electronics

Secured to PCB with thermally conductive adhesive tape

Conductor block expands/contracts vertically to compensate for tolerance stack up and optimizes surface contact and pressure along the thermal path; eliminates the need for a thermal gap pad

Compatible with Interscale C enclosures

## CARATERÍSTICAS DO PRODUTO

Product Type: Conductor Block

Família de produtos: Interscale

Tipo: Heat Conductor

Works With: Cases

Quantidade por embalagem: 1

Profundidade: 22mm

Largura: 22mm

Acabamento: Anodized; Aluminum-Zinc Plated

Gross Weight: 0.074kg

Material: Alumínio; Aço

## AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em [www.nVent.com](http://www.nVent.com) e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Middle East & India

Dubai, United Arab  
Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



O nosso forte portfólio de marcas:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**