RatiopacPRO/-Air Tip-up Handle, 63 HP

NÚMERO DE CATÁLOGO

24571-321

Tip-up carrying handles.

CERTIFICATIONS

RoHS COMPLIANT

CARACTERISTICAS

- Adjustable in 30° increments
- Retrofittable without mechanical tooling on case
- Static load-carrying capacity 30 kg
- The handle enable a user to have a better view to the front side of the case in case of desktop usage

CARATERÍSTICAS DO PRODUTO

- Rack Width: 63HP
- Quantidade por embalagem: 1
- Tipo de alça: Tip-up Handle
- Cor: Silver
- Acabamento: Pintura electrostática com Acabamento Texturado
- Material: Aluminio; ABS
- Família de produtos: RatiopacPRO; RatiopacPRO AIR
- Product Type: Handle

Works With: Cases

Gross Weight: 0.561kg

DETALHES ADICIONAIS DO PRODUTO

Cannot be used in conjunction with front handles.

Assembly kit is required for tip-up carrying handle, please order separately.

AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

North America
All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe
Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia
Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India
Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff

O nosso forte portefólio de marcas:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.