

# MTCA Guide Rail

Guide rail for MicroTCA.0, MicroTCA.1 and MicroTCA.4.



## CERTIFICATIONS



## CARACTERISTICAS

Guide rail for MicroTCA.0, MicroTCA.1 and MicroTCA.4

Easy installation without tools in 1 HP grid; the minimum distance between two guide rails is 3 HP (compact)

## ESPECIFICAÇÕES

Table 1/1

Número de catálogo	Tipo	Works With	Material	Cor	Quantidade por embalagem
20849-198	MicroTCA Carrier Hub	MicroTCA Systems	Polybutylene Terephthalate	Grey	10
20849-202	MicroTCA Carrier Hub	MicroTCA Systems	Polybutylene Terephthalate	Grey	10
20849-194	MicroTCA AdvancedMC	MicroTCA Systems	Polybutylene Terephthalate	Vermelho	10
20849-196	MicroTCA Power Supply	MicroTCA Systems	Polybutylene Terephthalate	Yellow	10
20849-200	MicroTCA Universal	MicroTCA Systems	Polybutylene Terephthalate	Green	10

Número de catálogo	Tipo	Works With	Material	Cor	Quantidade por embalagem
20849-201	MicroTCA Universal	MicroTCA Systems	Polybutylene Terephthalate	Green	100
20849-195	MicroTCA AdvancedMC	MicroTCA Systems	Polybutylene Terephthalate	Vermelho	100

## AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em [www.nVent.com](http://www.nVent.com) e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



O nosso forte portefólio de marcas:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**