

# 19" Front Panel, Plastic



19" plastic made clip on Front Panels with esthetic design are specially made for the datacom vertical. The easy clip on panels help in air flow management and also simultaneously providing an appealing look for the network rack.

## CERTIFICATIONS



## CARACTERISTICAS

Attractive design

Simple fitting by clipping onto the 19" plane

## ESPECIFICAÇÕES

**Accessory Type:** Front panel

Table 1/3

Número de catálogo	Tipo	Instalação	EMC Shielding	Material	Front Finish	Rear Finish
87927-991	19" Front Panel	Snapped in	Não	ABS	Raw	Raw
87927-992	19" Front Panel	Snapped in	Não	ABS	Raw	Raw
23130-623	19" Front Panel	Snapped in	Não	ABS		
23130-622	19" Front Panel	Snapped in	Não	ABS		

Table 2/3

Número de catálogo	Código de cor	Rack Height	Altura	Rack Width	Largura	Profundidade
--------------------	---------------	-------------	--------	------------	---------	--------------

87927-991	RAL 7035	1U	43.71mm	95HP	482mm	12mm
87927-992	RAL 7035	2U	88.17mm	95HP	482mm	12mm
23130-623	RAL 7035	6U	266.6mm	95HP	483mm	2mm
23130-622	RAL 9005	6U	266.6mm	95HP	483mm	2mm

Table 3/3

Número de catálogo	Quantidade por embalagem
87927-991	10
87927-992	10
23130-623	10
23130-622	10

## AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em [www.nVent.com](http://www.nVent.com) e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



O nosso forte portefólio de marcas:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**