

Interscale for Mini-ITX, Conduction Cooled



Small form factor case with integrated EMC-shielding and conduction cooling for Mini-ITX boards, based on the innovative and flexible nVent SCHROFF Interscale platform.

CERTIFICATIONS



CARACTERÍSTICAS

Modular case consisting of 3 easy to assemble parts; body, top cover and front panel

Cutout for Mini ITX I/O panel, power connector (Phoenix Contact, 0710028) and power switch (Schurter, MCS 18 Front)

Integrated EMC protection

Other dimensions, cutout shapes or locations, and screen printing available

Rigid construction requires only four screws

Board mounting studs installed

Color RAL 7016

ESPECIFICAÇÕES

Altura:	94mm
Profundidade:	189mm
Material:	Aluminio
Tipo:	Desktop
Família de produtos:	Interscale
Grau de proteção:	IP30
Código de cor:	RAL 7016
Product Type:	Small Form Factor Case

Table 1/1

Número de catálogo	Design Feature	Quantidade por embalagem	Cooling	Cor	Acabamento	Largura
14830-005	10 mm Fins	1	Conduction Cooled	Anthracite Grey	Pintura electrostática com Acabamento Texturado	184mm
14830-006	20 mm Fins	1	Conduction Cooled	Anthracite Grey	Pintura electrostática com Acabamento Texturado	184mm

DETALHES ADICIONAIS DO PRODUTO

Only the listed Interscale accessories are compatible.

Modified or customized cases up on request.

AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



O nosso forte portefólio de marcas:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE