


# Varistar CP Side Separating Wall



Side panel for side by side cabinets replacing 2 individual cabinet side panles. The seperating panel is mounted between to racks and fully compatible with all air blanking panels.

## CERTIFICATIONS



## CARACTERISTICAS

Prevents unauthorized access

For cabinets arranged in rows, wall replaces individual cabinet side walls

## ESPECIFICAÇÕES

**Acabamento:** Aluminum-Zinc Plated

**Product Type:** Cabinet/Rack Panel

**Material:** Aço

Table 1/1

Número de catálogo	Rack Height	Altura	Profundidade	Quantidade por embalagem	Tipo
23130-485	47U	2200mm	1200mm	1	Separating Wall
23130-484	47U	2200mm	1000mm	1	Separating Wall

Número de catálogo	Rack Height	Altura	Profundidade	Quantidade por embalagem	Tipo
23130-480	42U	2000mm	1000mm	1	Separating Wall
23130-508	42U	2000mm	1100mm	1	Separating Wall
23130-510	52U	2450mm	1100mm	1	Separating Wall
23130-509	47U	2200mm	1100mm	1	Separating Wall
23130-581	52U	2450mm	1200mm	1	Separating Wall
23130-580	52U	2450mm	1000mm	1	Separating Wall
23130-481	42U	2000mm	1200mm	1	Separating Wall

## AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em [www.nVent.com](http://www.nVent.com) e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



O nosso forte portefólio de marcas:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**