


DIN Rail

Data Solutions

A DIN rail is a standard metal rail widely used for mounting circuit breakers and industrial control equipment inside equipment racks.



CARACTERISTICI

Pre-Cut Lengths and with Perforations

Steel with electrogalvanized finishing

Comply with: EN 60715 Standards

SPECIFICAȚII

Product Type: DIN Rail

Table 1/2

Număr de catalog	Material	Height	Length	Finish	Package Quantity	Depth
20118-879	Oțel	35mm	175mm	Oțel Zincat	4	7.5mm
20118-874	Oțel	35mm	275mm	Oțel Zincat	4	15mm
20118-872	Oțel	35mm	125mm	Oțel Zincat	4	15mm
20118-883	Oțel	35mm	575mm	Oțel Zincat	4	7.5mm
20118-875	Oțel	35mm	375mm	Oțel Zincat	4	15mm
20118-878	Oțel	35mm	125mm	Oțel Zincat	4	7.5mm
20118-880	Oțel	35mm	275mm	Oțel Zincat	4	7.5mm
20118-877	Oțel	35mm	575mm	Oțel Zincat	4	15mm
20118-882	Oțel	35mm	475mm	Oțel Zincat	4	7.5mm

Număr de catalog	Material	Height	Length	Finish	Package Quantity	Depth
20118-873	Oțel	35mm	175mm	Oțel Zincat	4	15mm
20118-881	Oțel	35mm	375mm	Oțel Zincat	4	7.5mm
20118-876	Oțel	35mm	475mm	Oțel Zincat	4	15mm
20118-893	Oțel	35mm	375mm	Oțel Zincat	10	7.5mm
20118-892	Oțel	35mm	275mm	Oțel Zincat	10	7.5mm
20118-891	Oțel	35mm	175mm	Oțel Zincat	10	7.5mm
20118-890	Oțel	35mm	125mm	Oțel Zincat	10	7.5mm
20118-895	Oțel	35mm	575mm	Oțel Zincat	10	7.5mm
20118-894	Oțel	35mm	475mm	Oțel Zincat	10	7.5mm
20118-889	Oțel	35mm	575mm	Oțel Zincat	10	15mm
20118-887	Oțel	35mm	375mm	Oțel Zincat	10	15mm
20118-885	Oțel	35mm	175mm	Oțel Zincat	10	15mm
20118-886	Oțel	35mm	275mm	Oțel Zincat	10	15mm
20118-884	Oțel	35mm	125mm	Oțel Zincat	10	15mm
20118-888	Oțel	35mm	475mm	Oțel Zincat	10	15mm

Table 2/2

Număr de catalog	Width
20118-879	175mm
20118-874	275mm
20118-872	125mm
20118-883	575mm
20118-875	375mm
20118-878	125mm
20118-880	275mm
20118-877	575mm
20118-882	475mm
20118-873	175mm
20118-881	375mm
20118-876	475mm
20118-893	375mm
20118-892	275mm
20118-891	175mm
20118-890	125mm
20118-895	575mm

Număr de catalog	Width
20118-894	475mm
20118-889	575mm
20118-887	375mm
20118-885	175mm
20118-886	275mm
20118-884	125mm
20118-888	475mm

AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.



Portofoliul nostru puternic de mărci:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE