

# Varistar CP Deco Frame



The deco frame is a perfect fit for the Varistar CP without a front door. It conceals any cabling on the sides of the cabinet, streamlining cable routing and equipment mounting for a more efficient installation process and simultaneously improving the cabinet's appearance.

## CARACTERISTICI

Conceals cabling beside the 19" panel mount, streamlining cable routing and equipment mounting for a more efficient installation process

Provides easier access to the cabinet's internal components with hinged or removable panels, simplifying maintenance or repairs

Imparts improved functionality, appearance, and durability for Varistar CP cabinets without a door

Can be assembled at front and/or rear

## SPECIFICAȚII

- Static Load:** 400kgf
- Product Type:** Cabinet/Rack Frame
- Material:** Oțel

Table 1/2

Număr de catalog	Rack Height	Height	Width	Design Feature	Package Quantity	Color
21630-311	33U	1600mm	600mm	19" Plane Integrated	1	Black Grey
21630-920	47U	2200mm	800mm	Swing frame	1	Black Grey
21630-924	38U	1800mm	800mm	19" Slide Mounts	1	Black Grey
21630-309	24U	1200mm	600mm	19" Plane Integrated	1	Black Grey
21630-314	47U	2200mm	600mm	19" Plane Integrated	1	Black Grey

Număr de catalog	Rack Height	Height	Width	Design Feature	Package Quantity	Color
21630-926	47U	2200mm	800mm	19" Slide Mounts	1	Black Grey
21630-919	42U	2000mm	800mm	Swing frame	1	Black Grey
21630-313	42U	2000mm	600mm	19" Plane Integrated	1	Black Grey
21630-310	29U	1400mm	600mm	19" Plane Integrated	1	Black Grey
21630-918	38U	1800mm	800mm	Swing frame	1	Black Grey
21630-925	42U	2000mm	800mm	19" Slide Mounts	1	Black Grey
21630-312	38U	1800mm	600mm	19" Plane Integrated	1	Black Grey

Table 2/2

Număr de catalog	Color Code	Finish	Type
21630-311	RAL 7021	Vopsit Pulbere	Deco Frame
21630-920	RAL 7021	Vopsit Pulbere	Deco Frame
21630-924	RAL 7021	Vopsit Pulbere	Deco Frame
21630-309	RAL 7021	Vopsit Pulbere	Deco Frame
21630-314	RAL 7021	Vopsit Pulbere	Deco Frame
21630-926	RAL 7021	Vopsit Pulbere	Deco Frame
21630-919	RAL 7021	Vopsit Pulbere	Deco Frame
21630-313	RAL 7021	Vopsit Pulbere	Deco Frame
21630-310	RAL 7021	Vopsit Pulbere	Deco Frame
21630-918	RAL 7021	Vopsit Pulbere	Deco Frame
21630-925	RAL 7021	Vopsit Pulbere	Deco Frame
21630-312	RAL 7021	Vopsit Pulbere	Deco Frame

## DETALII SUPLIMENTARE DESPRE PRODUS

The deco frame provides easier access to the cabinet's internal components with hinged or removable panels, simplifying maintenance or repairs. It's an essential addition to any electronics cabinet without a front door, particularly for Automated Test Equipment, providing improved functionality, appearance, and durability.

## AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe [www.nvent.com](http://www.nvent.com) și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte

și/sau poate anula garanția dvs.

#### North America

All locations

+1.763.422.2661

Chat with us:

[nvent.com/schroff](https://nvent.com/schroff)

#### Europe

Straubenhardt, Germany

+49.7082.794.0

Betschdorf, France

+33.3.88.90.64.90

Warsaw, Poland

+48.22.209.98.35

Assago, Italy

+39.02.932.7141

Chat with us:

[nvent.com/schroff](https://nvent.com/schroff)

#### Asia

Shanghai, China

+86.21.2412.6943

Qingdao, China

+86.532.8771.6101

Singapore

+65.6768.5800

Shin-Yokohama, Japan

+81.45.476.0271

Chat with us:

[nvent.com/schroff](https://nvent.com/schroff)

#### Middle East & India

Dubai, United Arab Emirates

+971.4.378.1700

Bangalore, India

+91.80.6715.2001

Istanbul, Turkey

+90.216.250.7374

Chat with us:

[nvent.com/schroff](https://nvent.com/schroff)



Portofoliul nostru puternic de mărci:

**CADDY**

**ERICO**

**HOFFMAN**

**ILSCO**

**SCHROFF**

**TRACHTE**