

Intelligent iPDU, EN1850, 400 VAC, 3-PH, 32 A

Data Solutions

NUMĂR DE CATALOG

EN1850



Modular, compact intelligent PDU with inlet metering. Ultra-Low Profile Design

CARACTERISTICI

Enlogic EN1xxx Intelligent Power Distribution Units monitors input power of the entire PDU, provides billing grade unit level monitoring

High Visibility Data Display and Interactive Graphic Display

Measure circuit breaker loads across redundant feeds to avoid accidental downtime

Enables smart load balancing for power efficiency and maximized capacity utilization

Gigabit Ethernet Interface and redundant Ethernet (10/100)

iPDU DC power redundancy solution for up to 64 PDU's

Toolless Hot-Swap Controller

Input voltage 400 VAC, 3-phase

C13, C19 outlets

ATRIBUTE PRODUS

Product Family: Enlogic

Type: Intelligent PDU

Product Type: Socket Strip

Socket Type: (24) C13/C15; (24) C13/C15/C19/C21

Socket Quantity: 48

Color: Black

Circuit Breaker: 20 A, 1-pole, Hy-Mag

Switched Outlets: No

Circuit Breaker Quantity: 6

Power Rating: 17.3 kVA North America; 22.1 kVA International

Input Cable Length: 1.8m

Input Cable Location: Top Feed

Input Voltage: 380 – 415V

Phase: 3 PH

Max Power Input: 17.3 / 22.1 kVA

Nominal Voltage: 415V

On/Off Switch Included: No

Output Voltage: 208 – 230VAC

Amperage (Derated Amperage): 30 A (24 A) North America; 32 A International

Plug Type: IEC 60309 530P6/532P6

Rack Units: 0U

Removable Input Cable: No

Metering Type: Input

Material: Oțel

Finish: Vopsit Pulbere

Height: 1780mm

Width: 56mm

Depth: 55mm

Weight: 10.5kg

Package Quantity: 1

DETALII SUPLIMENTARE DESPRE PRODUS

Please order bracket for vertical mounting separately.

AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răni corporale grave și moarte și/sau poate anula garanția dvs.



Portofoliul nostru puternic de mărci:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE