


# MSP0 PDU, 2U, 60A(48A)NA/63A Int, 208V NA, 230V Int, 1P, 4 CB, (6)C13, (6)4-in-1

## Data Solutions

### NUMĂR DE CATALOG

### EN6354



The Advantage Series Outlet Metered, Outlet Switched PDU family offers energy metering with advanced power and environmental monitoring options and remote outlet on/off switching. Comprehensive monitoring at the input phase, circuit breaker, and individual outlet levels offers advanced alerts of potential overloads. Billing-grade metering provides accurate power consumption data for energy use optimization. The hot-swappable network management controller features Gigabit and redundant ethernet communication with advanced support for external environmental sensors and rack security access solutions.

### ATRIBUTE PRODUS

Product Family: Enlogic

Product Type: Socket Strip

Socket Type: (6) C13/C15; (6) C13/C15/C19/C21

Circuit Breaker: 20 A

Color: Black

Circuit Breaker Quantity: 4

Switched Outlets: Yes

Length: 87mm

Power Rating: 11.5 kVA North America; 14.5 kVA International

Interrupt Rating: 5kAIC

Number of Poles: 1

Input Voltage: 208V

Phase: 1 PH

Output Voltage: 208 – 230VAC

Plug Type: IEC 60309 360P6 (IP44)

Nominal Voltage: 230V

Removable Input Cable: No

Amperage (Derated Amperage): 60 A (48 A) North America; 63 A International

Rack Units: 2U

Type: Intelligent PDU

Finish: Vopsit Pulbere

Metering Type: Outlet

Material: Oțel

Height: 87mm

Weight: 8kg

Width: 444mm

Depth: 269mm

Package Quantity: 1

Input Cable Length: 3m

## DETALII SUPLIMENTARE DESPRE PRODUS

---

87 mm L x 444 mm W x 269 mm D, (269 mm D at CB)

## AVERTIZARE

---

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe [www.nvent.com](http://www.nvent.com) și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.



Portofoliul nostru puternic de mărci:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**