

PCB Bracket



The PCB support brackets enable the fixing of a PCB to front panel. Available in different materials.

CERTIFICATIONS



CARACTERISTICI

For fixing PCB to front panel

SPECIFICAȚII

Product Type: Bracket
Works With: Front Panels
Type: PCB Bracket

Table 1/2

Număr de catalog	Material	Package Quantity	Flammability Rating	Depth	Height	Width
60807-181	Zinc Alloy	1		8.6mm	11.1mm	10.2mm
60807-203	Zinc Alloy	1				
60807-183	Polybutylene Terephthalate	1	UL® 94V-0			
60807-011	Lexan	1	UL® 94V-0			
60807-211	Polybutylene Terephthalate	1	UL® 94V-0			

Table 2/2

Număr de catalog	Thread Size	Thread Type
60807-181	M2.5	Metric
60807-203		
60807-183		
60807-011		
60807-211		

DETALII SUPLIMENTARE DESPRE PRODUS

Delivery is in standard pack multiples. Pricing is per individual item.

AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O

instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Portofoliul nostru puternic de mărci:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE