


Varistar CP Mounting Plate



Varistar Mounting Plate for mounting electrical components and sub-assemblies, with 600 kg load capacity. The mounting plate can also be rear mounted and strengthening bracket can be added to increase load capacity.

CERTIFICATIONS



CARACTERISTICI

For mounting electrical components and sub-assemblies including cabling

Mounting pitch 25 mm in depth and 50 mm in height for partial-height mounting

Static load-carrying capacity up to 450 kg (rear mounted)

600 kg at full height, mounted to rear, with additional strengthening brackets

Strengthening bracket increases static load-carrying capacity

SPECIFICAȚII

Product Type: Mounting Plate

Material: Oțel

Table 1/1

Număr de catalog	Height	Width	Package Quantity	Finish
23130-407	2000mm	600mm	1	Oțel Zincat
23130-405	1800mm	600mm	1	Oțel Zincat
23130-414	1200mm	800mm	1	Oțel Zincat
23130-408	2000mm	800mm	1	Oțel Zincat
23130-413	1200mm	600mm	1	Oțel Zincat
23130-406	1800mm	800mm	1	Oțel Zincat

DETALII SUPLIMENTARE DESPRE PRODUS

Depth members are required for partial-height mounting.

AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Portofoliul nostru puternic de mărci:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE