

# Intelligent iPDU, EN2403, 400 VAC, 3-PH, 16 A

## Data Solutions

### KATALOGOVÉ ČÍSLO

## EN2403

Modular, compact intelligent PDU with inlet metering. Ultra-Low Profile Design

### VLASTNOSTI

Enlogic EN2xxx Intelligent Power Distribution Units monitors input power of the entire PDU and offers remote switching of individual outlets, provides billing grade unit level monitoring

High Visibility Data Display and Interactive Graphic Display

Measure circuit breaker loads across redundant feeds to avoid accidental downtime

Enables smart load balancing for power efficiency and maximized capacity utilization

Gigabit Ethernet Interface and redundant Ethernet (10/100)

iPDU DC power redundancy solution for up to 64 PDU's

Toolless Hot-Swap Controller

Input voltage 400 VAC, 3-phase

C13, C19 outlets

### VLASTNOSTI PRODUKTU

Produktová řada: Enlogic

Typ: Intelligent PDU

Product Type: Socket Strip

Typ zásuvky: (30) C13; (6) C19

Socket Quantity: 36

Barva: Black

Circuit Breaker: 16 A, 1-pole, Hy-Mag

Switched Outlets: Yes

Circuit Breaker Quantity: 0

Input Cable Location: Top Feed

Input Voltage: 400V

Phase: 3 PH WYE

Max Power Input: 11.0 kVA

Output Voltage: 200 – 240VAC

Plug Type: IEC 60309 516P6 (IP44)

Amperage (Derated Amperage): 16 A

Rack Units: 0U

Removable Input Cable: No

Metering Type: Input

Množství v balení: 1

Interrupt Rating: 5kAIC

## DALŠÍ PODROBNOSTI O PRODUKTU

---

Please order bracket for vertical mounting separately.

## UPOZORNĚNÍ

---

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na [www.nvent.com](http://www.nvent.com) a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.



Naše portfolio silných značek:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**