

# Single Pole Distribution Block

## Power Utilities



### CERTIFICERINGER



### FUNKTIONER

Tinned copper or aluminum block allows for copper or aluminum conductor direct connections, or using ferrule

Screw retaining cover is hinged and removable

Design allows for visual inspection of conductor and confirmation of connection

Modular snap-together blocks for building multi-pole power blocks

Easily clips onto DIN rail or mounts to panel with screws

95% fill ratio

RoHS compliant

Conforms to EN 45545 obtaining an HL3 classification for chapter R23 and HL2 classification for chapter R22

Halogen free

## SPECIFIKATIONER

**Finish:** Tinned

Table 1/2

Katalognummer	Artikelnummer	Max Current Rating, IEC	Max Current Rating, UL/CSA	Line Side Connection	Load Side Connection	Materiale
UD2C12C630AL	569205	630A	670A	2 Cables	12 Cables	Aluminium, Thermoplastic
UD-400A	569050	400A	335A	Cable	11 Cables	Copper, Thermoplastic
UDF12C800AL	569208	800A	670A	Flat Conductor	12 Cables	Aluminium, Thermoplastic

Table 2/2

Katalognummer	Artikelnummer	Line Side Max Conductor Size, IEC	Load Side Max Conductor Size, IEC	Max Working Voltage, IEC (Ui)	Max Working Voltage, UL (Vin)	Certificeringer
UD2C12C630AL	569205	185 mm <sup>2</sup>	25 mm <sup>2</sup>	1000, 1500	1000	UL, cUL, QPQS7.E49727 6
UD-400A	569050	185 mm <sup>2</sup>	35 mm <sup>2</sup>	1000	600	CSA, UR, CE, ERIFLEX UD, cUR, RoHS
UDF12C800AL	569208	240 mm <sup>2</sup>	25 mm <sup>2</sup>	1000, 1500	1000	cUL, QPQS7.E49727 6, UL

## YDERLIGERE PRODUKTOPLYSNINGER

Increase the number of outputs with one input using a jumper on blocks with a Max Current Rating, IEC up to 160 A.

Blocks with 1,000 VAC/DC Max Working Voltage, UL are ideal for solar applications.

### Design Guideline for Distribution Blocks, Power Blocks and Power Terminals

Derating according to Ambient\* Temperature (°C) to maintain working temperature of 85°C

Ambient Temperature (°C)	30°	35°	40°	45°	50°	55°	60°	65°	70°	75°
Derating Coefficient (d)	1	1	1	0.94	0.88	0.82	0.75	0.67	0.58	0.47

\*environment around the terminal blocks inside the enclosure

## ADVARSEL

---

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på [www.nvent.com](http://www.nvent.com) og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden unkladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.



Vores kraftfulde portefølje af mærker:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**