

# MTCA.4 System for 12 Double Full-Size AMC Modules



The system is designed for high-performance, high availability applications. The hot-swap fan modules with EMMC in pull configuration ensure that the front and rear slots are properly cooled. The fan speed is adjustable via the MCH. The separate JSM installation space prevents an AMC slot from being occupied by a JTAG module. The system can take up to four power modules to ensure a sufficient power supply for demanding applications. The backplane features clock and trigger lines.

## CERTIFICERINGER



## FUNKTIONER

In accordance with MTCA.4 R1.0 specification

84 HP system for 12 double Full-Size AdvancedMC modules, 2 Single Full-Size MCHs, and 4 / 2 Single Full-Size power modules

6 rear transition module slots for Double Full-Size RTMs

1 Single Full-Size slot for a JTAG switch module (JSM)

Backplane with dual-star topology

Optional fan speeds for front and rear sections can be separately adjusted via the MCH

2 hot-swap fan modules with cooling unit manager (CU EMMC)

Air filter accessible from the front

## SPECIFIKATIONER

Table 1/3

Katalognummer	Product Type	Number of Slots	Type	Backplane Type	Data Transfer	Power per Slot

11890-170	System	12	19" Rack Mount	MTCA.4 Dual Star Topology, JSM	40 GbE, PCIe Gen3	80W
11890-156	System	12	19" Rack Mount	CMS Dual Star Topology, JSM	40 GbE, PCIe Gen3	80W
11890-152	System	12	19" Rack Mount	MTCA.4 Dual Star Topology, JSM	40 GbE, PCIe Gen3	80W
11890-119	System	12	19" Rack Mount	CMS Dual Star Topology, JSM	40 GbE, PCIe Gen3	80W

Table 2/3

Katalognummer	Airflow Direction	Rack Height	Power Supply Type	Power Supply Included	Rear I/O	Complies With
11890-170	Front to Rear	9U	2 x (4) Single Full-size PM	No	Yes	PICMG MTCA.4 R1.0
11890-156	Front to Rear	9U	2 x (4) Single Full-size PM	No	Yes	PICMG MTCA.4 R1.0
11890-152	Bottom to Top	7U	2 x (4) Single Full-size PM	No	Yes	PICMG MTCA.4 R1.0
11890-119	Bottom to Top	7U	2 x (4) Single Full-size PM	No	Yes	PICMG MTCA.4 R1.0

Table 3/3

Katalognummer	Dybde	Pakke mængde
11890-170	373mm	1
11890-156	373mm	1
11890-152	373mm	1
11890-119	373mm	1

## YDERLIGERE PRODUKTOPLYSNINGER

2 Power Supplies are required to operate the system.

Modified systems available on request.

## ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på [www.nvent.com](http://www.nvent.com) og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden unkladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

### North America

All locations

+1.763.422.2661

Chat with us:

[nvent.com/schroff](https://nvent.com/schroff)

### Europe

Straubenhardt, Germany

+49.7082.794.0

Betschdorf, France

+33.3.88.90.64.90

Warsaw, Poland

+48.22.209.98.35

Assago, Italy

+39.02.932.7141

Chat with us:

[nvent.com/schroff](https://nvent.com/schroff)

### Asia

Shanghai, China

+86.21.2412.6943

Qingdao, China

+86.532.8771.6101

Singapore

+65.6768.5800

Shin-Yokohama, Japan

+81.45.476.0271

Chat with us:

[nvent.com/schroff](https://nvent.com/schroff)

### Middle East & India

Dubai, United Arab

Emirates

+971.4.378.1700

Bangalore, India

+91.80.6715.2001

Istanbul, Turkey

+90.216.250.7374

Chat with us:

[nvent.com/schroff](https://nvent.com/schroff)



Vores kraftfulde portefølje af mærker:

**CADDY**

**ERICO**

**HOFFMAN**

**ILSCO**

**SCHROFF**

**TRACHTE**