

DT Panel Protector (B), 240 kA

Data Solutions



The nVent ERICO DTX240 Series of Surge Protective Devices (SPD) North American and Worldwide standards compliance and provides premium protection against damaging transients and surge currents, particularly in IEC Class I & Class II and UL Type 1 & Type 2 locations. The innovative design allows for installation on the line or load of the service panels and removes the need for circuit breakers (B Version Only). With a 240 kA per phase surge rating, DTX240 is well suited for category C locations. It is typically used in applications including service entrances, distribution, branch panels, MCC, lighting panels, HVAC, and more. The nVent ERICO DTX240 also features a NEMA®-4X enclosure rating, making it suitable for outdoor applications.

CERTIFICATIONS



FEATURES

Excellent clamping and low UL voltage protection ratings

Features relay alarming for power/phase loss and status of SPD health

Design allows for easy removal and replacement of surge modules via lever assist

RS-485 Interface Standard

10 Year Warranty

SPECIFICATIONS

Table 1/2

| | | | | | | |
|-----------------------|-------------------------|--------------------|--------------------|-------------------------|--------------------|--------------------|
| Catalog Number | DTX240B12024 OSP | DTX240B240D | DTX240B480D | DTX240B12024 OHD | DTX240B208Y | DTX240B480Y |
|-----------------------|-------------------------|--------------------|--------------------|-------------------------|--------------------|--------------------|

| | | | | | | |
|---|---------------------|------------------|------------------|---------------------|---------------------|---------------------|
| Nominal System Voltage (Un) | 120/240 V | 240 V | 480 V | 120/240 V | 120/208 V | 277/480 V |
| Distribution System | 1Ph 3W+G | 3PhΔ 3W+G | 3PhΔ 3W+G | 3PhΔ 4W+G | 3Ph 4W+G | 3Ph 4W+G |
| Max Continuous Operating Voltage (Uc) | 150/300 VAC | 275 VAC | 510 VAC | 150/275 VAC | 150/300 VAC | 350/700 VAC |
| Nominal Discharge Current (In), UL | 20kA 8/20 μs | 20kA 8/20 μs | 20kA 8/20 μs | 20kA 8/20 μs | 20kA 8/20 μs | 20kA 8/20 μs |
| Max Discharge Current (Imax), Per Phase | 240kA 8/20 μs | 240kA 8/20 μs | 240kA 8/20 μs | 240kA 8/20 μs | 240kA 8/20 μs | 240kA 8/20 μs |
| Impulse Current (Iimp), Per Mode | 12.5kA 10/350 μs | 12.5kA 10/350 μs | 12.5kA 10/350 μs | 12.5kA 10/350 μs | 12.5kA 10/350 μs | 12.5kA 10/350 μs |
| Frequency | 50 – 60Hz | 50 – 60Hz | 50 – 60Hz | 50 – 60Hz | 50 – 60Hz | 50 – 60Hz |
| Voltage Protection Rating (VPR), L-G | 700V | 1000V | 1800V | 1200V | 700V | 1200V |
| Voltage Protection Rating (VPR), L-L | 1000V | 1000V | 1800V | 1500V | 1200V | 1800V |
| Voltage Protection Rating (VPR), L-N | 600V | | | 800V | 700V | 1200V |
| Voltage Protection Rating (VPR), N-G | 600V | | | 1500V | 700V | 1200V |
| Protection Modes | L-N L-PE N-PE | L-PE | L-PE | L-N L-PE N-PE | L-N L-PE N-PE | L-N L-PE N-PE |
| Short Circuit Current Rating (SCCR) | 200kA | 200kA | 200kA | 200kA | 200kA | 200kA |
| Nominal Discharge Current (In), IEC | 40kA 8/20 μs | 40kA 8/20 μs | 40kA 8/20 μs | 40kA 8/20 μs | 40kA 8/20 μs | 40kA 8/20 μs |

| | | | | | | |
|--------------------------------------|-----------------------------------|-----------------------------------|-----------------------------------|-----------------------------------|-----------------------------------|-----------------------------------|
| Voltage Protection Level (Up), IEC | 1200 V @ 20 kA 3000 V @ 100 kA | 1200 V @ 20 kA 3000 V @ 100 kA | 1200 V @ 20 kA 3000 V @ 100 kA | 1200 V @ 20 kA 3000 V @ 100 kA | 1200 V @ 20 kA 3000 V @ 100 kA | 1200 V @ 20 kA 3000 V @ 100 kA |
| Short Circuit Current Rating (Iscrr) | 50kA | 50kA | 50kA | 50kA | 50kA | 50kA |
| Temperature | -40 to 80°C | -40 to 80°C | -40 to 80°C | -40 to 80°C | -40 to 80°C | -40 to 80°C |
| Enclosure Material | Metal with PC Lid | Metal with PC Lid | Metal with PC Lid | Metal with PC Lid | Metal with PC Lid | Metal with PC Lid |
| Enclosure Rating | NEMA®-4X UL® 50E Type 4 | NEMA®-4X UL® 50E Type 4 | NEMA®-4X UL® 50E Type 4 | NEMA®-4X UL® 50E Type 4 | NEMA®-4X UL® 50E Type 4 | NEMA®-4X UL® 50E Type 4 |

Table 2/2


| Catalog Number | DTX240B12024 OSP | DTX240B240D | DTX240B480D | DTX240B12024 OHD | DTX240B208Y | DTX240B480Y |
|-----------------------------------|--|--|--|--|--|--|
| Lead Size | 2.5 – 16mm ² | 2.5 – 16mm ² | 2.5 – 16mm ² | 2.5 – 16mm ² | 2.5 – 16mm ² | 2.5 – 16mm ² |
| Mounting | 8 Screw Locations | 8 Screw Locations | 8 Screw Locations | 8 Screw Locations | 8 Screw Locations | 8 Screw Locations |
| Remote Contact Switching Capacity | 2.0 A @ 240 V | 2.0 A @ 240 V | 2.0 A @ 240 V | 2.0 A @ 240 V | 2.0 A @ 240 V | 2.0 A @ 240 V |
| Remote Contacts | Yes (Form C) | Yes (Form C) | Yes (Form C) | Yes (Form C) | Yes (Form C) | Yes (Form C) |
| Status Indication | Audible alarm with silence switch Dual color status LED Mechanical flag OLED Display Surge/TOV Counter, Resettable | Audible alarm with silence switch Dual color status LED Mechanical flag OLED Display Surge/TOV Counter, Resettable | Audible alarm with silence switch Dual color status LED Mechanical flag OLED Display Surge/TOV Counter, Resettable | Audible alarm with silence switch Dual color status LED Mechanical flag OLED Display Surge/TOV Counter, Resettable | Audible alarm with silence switch Dual color status LED Mechanical flag OLED Display Surge/TOV Counter, Resettable | Audible alarm with silence switch Dual color status LED Mechanical flag OLED Display Surge/TOV Counter, Resettable |
| Technology | Hybrid technology utilizing thermal disconnects | Hybrid technology utilizing thermal disconnects | Hybrid technology utilizing thermal disconnects | Hybrid technology utilizing thermal disconnects | Hybrid technology utilizing thermal disconnects | Hybrid technology utilizing thermal disconnects |
| Certification Details | CSA C22.2 No. 269.2 UL® 1449 Edition 5 Type 1/2, 20 kA Mode | CSA C22.2 No. 269.2 UL® 1449 Edition 5 Type 1/2, 20 kA Mode | CSA C22.2 No. 269.2 UL® 1449 Edition 5 Type 1/2, 20 kA Mode | CSA C22.2 No. 269.2 UL® 1449 Edition 5 Type 1/2, 20 kA Mode | CSA C22.2 No. 269.2 UL® 1449 Edition 5 Type 1/2, 20 kA Mode | CSA C22.2 No. 269.2 UL® 1449 Edition 5 Type 1/2, 20 kA Mode |

| Catalog Number | DTX240B12024 OSP | DTX240B240D | DTX240B480D | DTX240B12024 OHD | DTX240B208Y | DTX240B480Y |
|--------------------|---|---|---|---|---|---|
| Complies With | ANSI®/IEEE® C62.41.2-2002 Cat A, Cat B, Cat C ANSI®/IEEE® C62.41.1-2002 Cat A, Cat B, Cat C ANSI®/IEEE® C62.45-2002 Cat A, Cat B, Cat C EN 61643-11 Type 2 IEC® 61643-11 Class II | ANSI®/IEEE® C62.41.2-2002 Cat A, Cat B, Cat C ANSI®/IEEE® C62.41.1-2002 Cat A, Cat B, Cat C ANSI®/IEEE® C62.45-2002 Cat A, Cat B, Cat C EN 61643-11 Type 2 IEC® 61643-11 Class II | ANSI®/IEEE® C62.41.2-2002 Cat A, Cat B, Cat C ANSI®/IEEE® C62.41.1-2002 Cat A, Cat B, Cat C ANSI®/IEEE® C62.45-2002 Cat A, Cat B, Cat C EN 61643-11 Type 2 IEC® 61643-11 Class II | ANSI®/IEEE® C62.41.2-2002 Cat A, Cat B, Cat C ANSI®/IEEE® C62.41.1-2002 Cat A, Cat B, Cat C ANSI®/IEEE® C62.45-2002 Cat A, Cat B, Cat C EN 61643-11 Type 2 IEC® 61643-11 Class II | ANSI®/IEEE® C62.41.2-2002 Cat A, Cat B, Cat C ANSI®/IEEE® C62.41.1-2002 Cat A, Cat B, Cat C ANSI®/IEEE® C62.45-2002 Cat A, Cat B, Cat C EN 61643-11 Type 2 IEC® 61643-11 Class II | ANSI®/IEEE® C62.41.2-2002 Cat A, Cat B, Cat C ANSI®/IEEE® C62.41.1-2002 Cat A, Cat B, Cat C ANSI®/IEEE® C62.45-2002 Cat A, Cat B, Cat C EN 61643-11 Type 2 IEC® 61643-11 Class II |
| Depth (D) | 98.3mm | 98.3mm | 98.3mm | 98.3mm | 98.3mm | 98.3mm |
| Height (H) | 330.7mm | 330.7mm | 330.7mm | 330.7mm | 330.7mm | 330.7mm |
| Width (W) | 222.5mm | 222.5mm | 222.5mm | 222.5mm | 222.5mm | 222.5mm |
| Unit Weight | 4.98kg | 5.18kg | 5.3kg | 5.38kg | 5.38kg | 5.45kg |
| Replacement Module | DT2180DTXM | DT2275DTXM | DT2510DTXM | DT2180DTXM DT2275DTXM | DT2150DTXM | DT2350M |

ADDITIONAL PRODUCT DETAILS

Optional Flush Plate and Side Mount Kits available: DTX240FP & DTX240SM

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE