

Plug-In Units Front Panel for Handle Form 1



Flat front panel. Enables the assembly of form 1 trapezoid form extraction handle. The front panel can be shielded with a textile gasket.

CERTIFICATIONS



FEATURES

Front panel, unshielded

Front panel, Al, 2.5 mm, front anodized, rear conductive

SPECIFICATIONS

- Material:** Aluminum
- Finish:** Anodized; Passivated
- Accessory Type:** Front panel
- Product Type:** Front Panel
- Type:** Front Panel with Handle (PIU)

Table 1/3

| Catalog Number | Rack Height | Rack Width | Package Quantity | Handle Type | Mounting | Front Finish |
|----------------|-------------|------------|------------------|-------------------|----------------|--------------|
| 30847-670 | 6U | 8HP | 1 | Trapezoid, Type 1 | Screw-on Front | Anodized |
| 30847-660 | 3U | 5HP | 1 | Trapezoid, Type 1 | Screw-on Front | Anodized |

| Catalog Number | Rack Height | Rack Width | Package Quantity | Handle Type | Mounting | Front Finish |
|----------------|-------------|------------|------------------|-------------------|----------------|--------------|
| 30847-667 | 6U | 5HP | 1 | Trapezoid, Type 1 | Screw-on Front | Anodized |
| 30847-668 | 6U | 6HP | 1 | Trapezoid, Type 1 | Screw-on Front | Anodized |
| 30847-666 | 6U | 4HP | 1 | Trapezoid, Type 1 | Screw-on Front | Anodized |
| 30847-669 | 6U | 7HP | 1 | Trapezoid, Type 1 | Screw-on Front | Anodized |
| 30847-665 | 3U | 12HP | 1 | Trapezoid, Type 1 | Screw-on Front | Anodized |
| 30847-664 | 3U | 10HP | 1 | Trapezoid, Type 1 | Screw-on Front | Anodized |
| 30847-671 | 6U | 10HP | 1 | Trapezoid, Type 1 | Screw-on Front | Anodized |
| 30847-663 | 3U | 8HP | 1 | Trapezoid, Type 1 | Screw-on Front | Anodized |
| 30847-672 | 6U | 12HP | 1 | Trapezoid, Type 1 | Screw-on Front | Anodized |
| 30847-661 | 3U | 6HP | 1 | Trapezoid, Type 1 | Screw-on Front | Anodized |
| 30847-659 | 3U | 4HP | 1 | Trapezoid, Type 1 | Screw-on Front | Anodized |
| 30847-662 | 3U | 7HP | 1 | Trapezoid, Type 1 | Screw-on Front | Anodized |

Table 2/3

| Catalog Number | Rear Finish | Treated Edges | Complies With | Depth (D) | EMC Shielding | Height (H) |
|----------------|-------------|---------------|---------------------------------|-----------|---------------|------------|
| 30847-670 | Conductive | No | IEC 60297-3-101, IEEE 1101.1/11 | 2.5mm | No | 261.8mm |
| 30847-660 | Conductive | No | IEC 60297-3-101, IEEE 1101.1/11 | 2.5mm | No | 128.4mm |
| 30847-667 | Conductive | No | IEC 60297-3-101, IEEE 1101.1/11 | 2.5mm | No | 261.8mm |
| 30847-668 | Conductive | No | IEC 60297-3-101, IEEE 1101.1/11 | 2.5mm | No | 261.8mm |

| Catalog Number | Rear Finish | Treated Edges | Complies With | Depth (D) | EMC Shielding | Height (H) |
|----------------|-------------|---------------|---------------------------------|-----------|---------------|------------|
| 30847-666 | Conductive | No | IEC 60297-3-101, IEEE 1101.1/11 | 2.5mm | No | 261.8mm |
| 30847-669 | Conductive | No | IEC 60297-3-101, IEEE 1101.1/11 | 2.5mm | No | 261.8mm |
| 30847-665 | Conductive | No | IEC 60297-3-101, IEEE 1101.1/11 | 2.5mm | No | 128.4mm |
| 30847-664 | Conductive | No | IEC 60297-3-101, IEEE 1101.1/11 | 2.5mm | No | 128.4mm |
| 30847-671 | Conductive | No | IEC 60297-3-101, IEEE 1101.1/11 | 2.5mm | No | 261.8mm |
| 30847-663 | Conductive | No | IEC 60297-3-101, IEEE 1101.1/11 | 2.5mm | No | 128.4mm |
| 30847-672 | Conductive | No | IEC 60297-3-101, IEEE 1101.1/11 | 2.5mm | No | 261.8mm |
| 30847-661 | Conductive | No | IEC 60297-3-101, IEEE 1101.1/11 | 2.5mm | No | 128.4mm |
| 30847-659 | Conductive | No | IEC 60297-3-101, IEEE 1101.1/11 | 2.5mm | No | 128.4mm |
| 30847-662 | Conductive | No | IEC 60297-3-101, IEEE 1101.1/11 | 2.5mm | No | 128.4mm |

Table 3/3

| Catalog Number | Width (W) |
|----------------|-----------|
| 30847-670 | 40.3mm |
| 30847-660 | 25mm |
| 30847-667 | 25mm |
| 30847-668 | 30.1mm |
| 30847-666 | 20mm |
| 30847-669 | 35.2mm |
| 30847-665 | 60.6mm |
| 30847-664 | 50.5mm |

| Catalog Number | Width (W) |
|----------------|-----------|
| 30847-671 | 50.5mm |
| 30847-663 | 40.3mm |
| 30847-672 | 60.6mm |
| 30847-661 | 30.1mm |
| 30847-659 | 20mm |
| 30847-662 | 35.2mm |

ADDITIONAL PRODUCT DETAILS

Please take into consideration that deliveries may be carried out in the stated SPQs (SPQ, e.g. 5 pieces, 10 pieces, 50 pieces, etc.). Differing order quantities (e.g. 2 pieces) may be changed to the next possible delivery quantity = Standard Pack Quantity.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations

+1.763.422.2661

Chat with us:

nvent.com/schroff

Europe

Straubenhardt, Germany

+49.7082.794.0

Betschdorf, France

+33.3.88.90.64.90

Warsaw, Poland

+48.22.209.98.35

Assago, Italy

+39.02.932.7141

Chat with us:

nvent.com/schroff

Asia

Shanghai, China

+86.21.2412.6943

Qingdao, China

+86.532.8771.6101

Singapore

+65.6768.5800

Shin-Yokohama, Japan

+81.45.476.0271

Chat with us:

nvent.com/schroff

Middle East & India

Dubai, United Arab

Emirates

+971.4.378.1700

Bangalore, India

+91.80.6715.2001

Istanbul, Turkey

+90.216.250.7374

Chat with us:

nvent.com/schroff



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE