


Power Terminal, Lug-to-Tunnel, 800 A

Data Solutions

CATALOG NUMBER

SBLT-800



CERTIFICATIONS



FEATURES

Tinned copper block allows for copper or aluminum conductor connections

Accessible studs and tunnels allow for easy connection of nVent ERIFLEX Flexibar and other conductors

Design allows for visual inspection of conductor and confirmation of connection

Voltage detection and measurement connection

Adjustable transparent cover

Modular snap-together blocks for building multi-pole power blocks

Easily clips onto DIN rail or mounts to panel with screws

SBLEC Power Terminals Fixing Accessory required for direct panel mount

RoHS compliant

Halogen free


PRODUCT ATTRIBUTES

Article Number: 561146
Material: Copper; Thermoplastic
Finish: Tinned
Max Current Rating, IEC: 1250A
Max Current Rating, UL/CSA: 760A
Short Term Withstand Current (Icw) 1s: 57.6kA
Peak Short Circuit Current (Ipk): 75kA
Short Circuit Current Rating (SCCR): 100kA
Max Working Voltage, IEC (Ui): 1000; 1500
Max Working Voltage, UL (Vin): 1000
Number of Stud Connections: 2
Stud Connection Conductor Width: (2) 20 – 40 mm; (1) 50 – 80 mm
Stud Connection Compact Stranded Wire Size: (2) 35 – 300 mm²
Stud Connection Wire Size: (2) #1 - 500 kcmil
Number of Tunnel Connections: 2
Tunnel Connection Compact Stranded Wire Size: (2) 95 – 240 mm²
Tunnel Connection Wire Size - Ferrule: (2) 50 – 185 mm²
Tunnel Connection Wire Size: (2) 3/0 – 500 kcmil
Depth (D): 75mm
Height (H): 205.7mm
Width (W): 115mm
A: 108mm
Unit Weight: 1.09kg
Certification Details: UL® 1059
Flammability Rating: UL® 94V-1
Complies With: IEC® 60947-7-1

ADDITIONAL PRODUCT DETAILS

Power terminal connections are interchangeable and can be used as line side or load side connections.

Design Guideline for Distribution Blocks, Power Blocks and Power Terminals										
Derating according to Ambient* Temperature (°C) to maintain working temperature of 85°C										
Ambient Temperature (°C)	30°	35°	40°	45°	50°	55°	60°	65°	70°	75°
Derating Coefficient (d)	1	1	1	0.94	0.88	0.82	0.75	0.67	0.58	0.47
*environment around the terminal blocks inside the enclosure										



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE