We connect and protect

Four Pole Distrib. Block with Threaded Bars, 125 A

Data Solutions

CATALOG NUMBER

TR-125A



CERTIFICATIONS

FEATURES

- Easily clips onto DIN rail or mounts to panel with screws
- Equipped with a current input plug
- Bolts included for output connections
- Transparent protection cover
- Easy accessibility for wiring
- Ready to use out of the box, saving installation time and labor
- RoHS compliant

PRODUCT ATTRIBUTES

Article Number: 563150

Material: Copper; Glass Fibre Reinforced Polyamide; Plexiglass
Max Working Voltage, IEC (Ui): 1000
Peak Short Circuit Current (Ipk): 40kA
Short Term Withstand Current (Icw) 1s: 8.4kA
Line Side Number of Connections: 1
Load Side Number of Connections: 5
Thread Size 1 (TS1): M5
Thread Size 2 (TS2): M6
Depth (D): 117mm
Height (H): 126mm
Width (W): 150mm
Unit Weight: 0.68kg
Flammability Rating: UL® 94V-0
Complies With: IEC® 60439.1; IEC® 61439.1; IEC® 60695-2-11 (Glow Wire Test 960 °C)

ADDITIONAL PRODUCT DETAILS

Thread Size 2 represents input plug.

Line side and load side number of connections are per pole.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.