


# CT Mounting Base



CTMB8001

CT Mounting Base accommodates the preference difference between line and load connections inside a CT cabinet. The bases are available in three variations of conductor connection styles to match your application: 1/2-in. studs on 1-3/4-in. centers, a model with mechanical lugs and a model with lugs on one side and studs on the other. Pre-punched mounting base holes align with the studs in a CT cabinet

## INDUSTRY STANDARDS

---

UL 414 Listed; File E240312

## FEATURES

---

Spacing for bar-type current transformer that conforms to ANSI 12.11

Conductor provisions: either mechanical lugs or 1/2-in. bolt on 1-3/4-in. centers with nut, spring and flat washer

Neutral bar with 10-32 tap screw

12-gauge galvanized formed base has electrically isolated mount/termination platform

## SPECIFICATIONS

Table 1/1

Catalog Number	Article Number	Material	Finish	Thickness	Connection Type	AIC (Ampere Interrupting Capacity) Rating
CTMB8001	14436	Mild Steel	Galvanized, Powder Coated		Studs	50000A
CTMB4001LS	15641	Mild Steel	Galvanized, Powder Coated	2.05mm	Lugs, Studs	50000A
CTMB4001L	15638	Mild Steel	Galvanized, Powder Coated	2.05mm	Lugs	50000A
CTMB8003	14437	Mild Steel	Galvanized, Powder Coated	2.05mm	Studs	50000A
CTMB8003L	14441	Mild Steel	Galvanized, Powder Coated	2.05mm	Lugs	50000A

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**