

# Front Panel, U-profile, Retrofit Shielding



U-profile front panel for textile EMC gasket.

## CERTIFICATIONS



## FEATURES

U-profile, front panel, Al, 2.5 mm, front anodized, rear conductive

For EMC textile gasket

## SPECIFICATIONS

|                        |                            |
|------------------------|----------------------------|
| <b>Depth (D):</b>      | 2.5mm                      |
| <b>Material:</b>       | Aluminum                   |
| <b>Finish:</b>         | Anodized; Passivated       |
| <b>Accessory Type:</b> | Front panel                |
| <b>Product Type:</b>   | Front Panel                |
| <b>Type:</b>           | Front Panel without Handle |
| <b>EMC Shielding:</b>  | No (Retrofittable)         |

Table 1/3

| Catalog Number | Rack Height | Rack Width | Package Quantity | Mounting | Gasket Type | Front Finish |
|----------------|-------------|------------|------------------|----------|-------------|--------------|
|----------------|-------------|------------|------------------|----------|-------------|--------------|

|           |    |      |   |                |             |          |
|-----------|----|------|---|----------------|-------------|----------|
| 30848-385 | 3U | 9HP  | 1 | Screw-on Front | Textile EMC | Anodized |
| 30848-354 | 3U | 4HP  | 1 | Screw-on Front | Textile EMC | Anodized |
| 20848-120 | 6U | 28HP | 1 | Screw-on Front | Textile EMC | Anodized |
| 30848-387 | 6U | 10HP | 1 | Screw-on Front | Textile EMC | Anodized |
| 20848-047 | 3U | 42HP | 1 | Screw-on Front | Textile EMC | Anodized |
| 20848-139 | 6U | 42HP | 1 | Screw-on Front | Textile EMC | Anodized |
| 20848-650 | 5U | 84HP | 1 | Screw-on Front | Textile EMC | Anodized |
| 30848-381 | 6U | 6HP  | 1 | Screw-on Front | Textile EMC | Anodized |
| 30848-386 | 3U | 10HP | 1 | Screw-on Front | Textile EMC | Anodized |
| 20848-160 | 6U | 63HP | 1 | Screw-on Front | Textile EMC | Anodized |
| 20848-649 | 5U | 63HP | 1 | Screw-on Front | Textile EMC | Anodized |
| 20848-269 | 4U | 42HP | 1 | Screw-on Front | Textile EMC | Anodized |
| 30848-380 | 3U | 6HP  | 1 | Screw-on Front | Textile EMC | Anodized |
| 20848-206 | 2U | 28HP | 1 | Screw-on Front | Textile EMC | Anodized |
| 30848-382 | 3U | 7HP  | 1 | Screw-on Front | Textile EMC | Anodized |
| 20848-270 | 4U | 42HP | 1 | Screw-on Front | Textile EMC | Anodized |
| 20848-648 | 5U | 42HP | 1 | Screw-on Front | Textile EMC | Anodized |
| 20848-262 | 2U | 84HP | 1 | Screw-on Front | Textile EMC | Anodized |
| 20848-027 | 3U | 28HP | 1 | Screw-on Front | Textile EMC | Anodized |
| 30848-384 | 3U | 9HP  | 1 | Screw-on Front | Textile EMC | Anodized |

Table 2/3

| Catalog Number | Rack Height | Rack Width | Package Quantity | Mounting       | Gasket Type | Front Finish |
|----------------|-------------|------------|------------------|----------------|-------------|--------------|
| 20848-647      | 5U          | 28HP       | 1                | Screw-on Front | Textile EMC | Anodized     |
| 20848-268      | 4U          | 28HP       | 1                | Screw-on Front | Textile EMC | Anodized     |
| 30848-383      | 6U          | 7HP        | 1                | Screw-on Front | Textile EMC | Anodized     |
| 20848-280      | 9U          | 84HP       | 1                | Screw-on Front | Textile EMC | Anodized     |
| 30848-357      | 6U          | 8HP        | 1                | Screw-on Front | Textile EMC | Anodized     |
| 20848-068      | 3U          | 63HP       | 1                | Screw-on Front | Textile EMC | Anodized     |
| 20848-260      | 2U          | 42HP       | 1                | Screw-on Front | Textile EMC | Anodized     |
| 20848-013      | 3U          | 14HP       | 1                | Screw-on Front | Textile EMC | Anodized     |
| 30848-359      | 6U          | 12HP       | 1                | Screw-on Front | Textile EMC | Anodized     |
| 30849-005      | 6U          | 3HP        | 1                | Screw-on Front | Textile EMC | Anodized     |
| 20848-189      | 6U          | 84HP       | 1                | Screw-on Front | Textile EMC | Anodized     |
| 20848-015      | 3U          | 16HP       | 1                | Screw-on Front | Textile EMC | Anodized     |

| Catalog Number | Rack Height | Rack Width | Package Quantity | Mounting       | Gasket Type | Front Finish |
|----------------|-------------|------------|------------------|----------------|-------------|--------------|
| 30848-378      | 3U          | 5HP        | 1                | Screw-on Front | Textile EMC | Anodized     |
| 20848-020      | 3U          | 21HP       | 1                | Screw-on Front | Textile EMC | Anodized     |
| 30849-004      | 3U          | 3HP        | 1                | Screw-on Front | Textile EMC | Anodized     |
| 30848-358      | 3U          | 12HP       | 1                | Screw-on Front | Textile EMC | Anodized     |
| 20848-106      | 6U          | 14HP       | 1                | Screw-on Front | Textile EMC | Anodized     |
| 30848-379      | 6U          | 5HP        | 1                | Screw-on Front | Textile EMC | Anodized     |
| 20848-108      | 6U          | 16HP       | 1                | Screw-on Front | Textile EMC | Anodized     |
| 30849-002      | 6U          | 2HP        | 1                | Screw-on Front | Textile EMC | Anodized     |

Table 3/3

| Catalog Number | Rack Height | Rack Width | Package Quantity | Mounting       | Gasket Type | Front Finish |
|----------------|-------------|------------|------------------|----------------|-------------|--------------|
| 30848-356      | 3U          | 8HP        | 1                | Screw-on Front | Textile EMC | Anodized     |
| 20848-097      | 3U          | 84HP       | 1                | Screw-on Front | Textile EMC | Anodized     |
| 20848-271      | 4U          | 84HP       | 1                | Screw-on Front | Textile EMC | Anodized     |
| 30848-355      | 6U          | 4HP        | 1                | Screw-on Front | Textile EMC | Anodized     |
| 20848-113      | 6U          | 21HP       | 1                | Screw-on Front | Textile EMC | Anodized     |
| 20848-261      | 2U          | 63HP       | 1                | Screw-on Front | Textile EMC | Anodized     |
| 30849-001      | 3U          | 2HP        | 1                | Screw-on Front | Textile EMC | Anodized     |

Table 1/3

| Catalog Number | Rear Finish | Treated Edges | Complies With                   | Height (H) | Width (W) | Certifications |
|----------------|-------------|---------------|---------------------------------|------------|-----------|----------------|
| 30848-385      | Conductive  | No            | IEC 60297-3-101, IEEE 1101.1/10 | 261.8mm    | 45.38mm   |                |
| 30848-354      | Conductive  | No            | IEC 60297-3-101, IEEE 1101.1/10 | 128.4mm    | 20mm      | RoHS           |
| 20848-120      | Conductive  | No            | IEC 60297-3-101, IEEE 1101.1/10 | 261.8mm    | 141.9mm   | RoHS           |
| 30848-387      | Conductive  | No            | IEC 60297-3-101, IEEE 1101.1/10 | 261.8mm    | 50.5mm    | RoHS           |
| 20848-047      | Conductive  | No            | IEC 60297-3-101, IEEE 1101.1/10 | 128.4mm    | 213mm     | RoHS           |

| Catalog Number | Rear Finish | Treated Edges | Complies With                   | Height (H) | Width (W) | Certifications |
|----------------|-------------|---------------|---------------------------------|------------|-----------|----------------|
| 20848-139      | Conductive  | No            | IEC 60297-3-101, IEEE 1101.1/10 | 261.8mm    | 213mm     | RoHS           |
| 20848-650      | Conductive  | No            | IEC 60297-3-101, IEEE 1101.1/10 | 217.4mm    | 426.4mm   |                |
| 30848-381      | Conductive  | No            | IEC 60297-3-101, IEEE 1101.1/10 | 261.8mm    | 30.1mm    | RoHS           |
| 30848-386      | Conductive  | No            | IEC 60297-3-101, IEEE 1101.1/10 | 128.4mm    | 50.5mm    | RoHS           |
| 20848-160      | Conductive  | No            | IEC 60297-3-101, IEEE 1101.1/10 | 261.8mm    | 319.7mm   | RoHS           |
| 20848-649      | Conductive  | No            | IEC 60297-3-101, IEEE 1101.1/10 | 217.4mm    | 319.7mm   |                |
| 20848-269      | Conductive  | No            | IEC 60297-3-101, IEEE 1101.1/10 | 172.9mm    | 213mm     | RoHS           |
| 30848-380      | Conductive  | No            | IEC 60297-3-101, IEEE 1101.1/10 | 128.4mm    | 30.1mm    | RoHS           |
| 20848-206      | Conductive  | No            | IEC 60297-3-101, IEEE 1101.1/10 | 84mm       | 141.9mm   |                |
| 30848-382      | Conductive  | No            | IEC 60297-3-101, IEEE 1101.1/10 | 128.4mm    | 35.2mm    | RoHS           |
| 20848-270      | Conductive  | No            | IEC 60297-3-101, IEEE 1101.1/10 | 172.9mm    | 213mm     | RoHS           |
| 20848-648      | Conductive  | No            | IEC 60297-3-101, IEEE 1101.1/10 | 217.4mm    | 213mm     |                |
| 20848-262      | Conductive  | No            | IEC 60297-3-101, IEEE 1101.1/10 | 84mm       | 426.4mm   | RoHS           |
| 20848-027      | Conductive  | No            | IEC 60297-3-101, IEEE 1101.1/10 | 128.4mm    | 141.9mm   | RoHS           |

| Catalog Number | Rear Finish | Treated Edges | Complies With                   | Height (H) | Width (W) | Certifications |
|----------------|-------------|---------------|---------------------------------|------------|-----------|----------------|
| 30848-384      | Conductive  | No            | IEC 60297-3-101, IEEE 1101.1/10 | 128.4mm    | 45.38mm   |                |

Table 2/3

| Catalog Number | Rear Finish | Treated Edges | Complies With                   | Height (H) | Width (W) | Certifications |
|----------------|-------------|---------------|---------------------------------|------------|-----------|----------------|
| 20848-647      | Conductive  | No            | IEC 60297-3-101, IEEE 1101.1/10 | 217.4mm    | 141.9mm   |                |
| 20848-268      | Conductive  | No            | IEC 60297-3-101, IEEE 1101.1/10 | 172.9mm    | 141.9mm   | RoHS           |
| 30848-383      | Conductive  | No            | IEC 60297-3-101, IEEE 1101.1/10 | 261.8mm    | 35.2mm    | RoHS           |
| 20848-280      | Conductive  | No            | IEC 60297-3-101, IEEE 1101.1/10 | 395.1mm    | 426.4mm   | RoHS           |
| 30848-357      | Conductive  | No            | IEC 60297-3-101, IEEE 1101.1/10 | 261.8mm    | 40.3mm    | RoHS           |
| 20848-068      | Conductive  | No            | IEC 60297-3-101, IEEE 1101.1/10 | 128.4mm    | 319.7mm   | RoHS           |
| 20848-260      | Conductive  | No            | IEC 60297-3-101, IEEE 1101.1/10 | 84mm       | 213mm     |                |
| 20848-013      | Conductive  | No            | IEC 60297-3-101, IEEE 1101.1/10 | 128.4mm    | 70.8mm    | RoHS           |
| 30848-359      | Conductive  | No            | IEC 60297-3-101, IEEE 1101.1/10 | 261.8mm    | 60.6mm    | RoHS           |
| 30849-005      | Conductive  | No            | IEC 60297-3-101, IEEE 1101.1/10 | 261.8mm    | 14.9mm    |                |
| 20848-189      | Conductive  | No            | IEC 60297-3-101, IEEE 1101.1/10 | 261.8mm    | 426.4mm   | RoHS           |
| 20848-015      | Conductive  | No            | IEC 60297-3-101, IEEE 1101.1/10 | 128.4mm    | 80.9mm    | RoHS           |

| Catalog Number | Rear Finish | Treated Edges | Complies With                   | Height (H) | Width (W) | Certifications |
|----------------|-------------|---------------|---------------------------------|------------|-----------|----------------|
| 30848-378      | Conductive  | No            | IEC 60297-3-101, IEEE 1101.1/10 | 128.4mm    | 25mm      | RoHS           |
| 20848-020      | Conductive  | No            | IEC 60297-3-101, IEEE 1101.1/10 | 128.4mm    | 106.3mm   | RoHS           |
| 30849-004      | Conductive  | No            | IEC 60297-3-101, IEEE 1101.1/10 | 128.4mm    | 14.9mm    | RoHS           |
| 30848-358      | Conductive  | No            | IEC 60297-3-101, IEEE 1101.1/10 | 128.4mm    | 60.6mm    | RoHS           |
| 20848-106      | Conductive  | No            | IEC 60297-3-101, IEEE 1101.1/10 | 261.8mm    | 70.8mm    | RoHS           |
| 30848-379      | Conductive  | No            | IEC 60297-3-101, IEEE 1101.1/10 | 261.8mm    | 25mm      | RoHS           |
| 20848-108      | Conductive  | No            | IEC 60297-3-101, IEEE 1101.1/10 | 261.8mm    | 80.9mm    | RoHS           |
| 30849-002      | Conductive  | No            | IEC 60297-3-101, IEEE 1101.1/10 | 261.8mm    | 9.8mm     | RoHS           |

Table 3/3

| Catalog Number | Rear Finish | Treated Edges | Complies With                   | Height (H) | Width (W) | Certifications |
|----------------|-------------|---------------|---------------------------------|------------|-----------|----------------|
| 30848-356      | Conductive  | No            | IEC 60297-3-101, IEEE 1101.1/10 | 128.4mm    | 40.3mm    | RoHS           |
| 20848-097      | Conductive  | No            | IEC 60297-3-101, IEEE 1101.1/10 | 128.4mm    | 426.4mm   | RoHS           |
| 20848-271      | Conductive  | No            | IEC 60297-3-101, IEEE 1101.1/10 | 172.9mm    | 426.4mm   | RoHS           |
| 30848-355      | Conductive  | No            | IEC 60297-3-101, IEEE 1101.1/10 | 261.8mm    | 20mm      | RoHS           |
| 20848-113      | Conductive  | No            | IEC 60297-3-101, IEEE 1101.1/10 | 261.8mm    | 106.3mm   | RoHS           |



### North America

All locations

+1.763.422.2661

Chat with us:

[nvent.com/schroff](https://nvent.com/schroff)

### Europe

Straubenhardt, Germany

+49.7082.794.0

Betschdorf, France

+33.3.88.90.64.90

Warsaw, Poland

+48.22.209.98.35

Assago, Italy

+39.02.932.7141

Chat with us:

[nvent.com/schroff](https://nvent.com/schroff)

### Asia

Shanghai, China

+86.21.2412.6943

Qingdao, China

+86.532.8771.6101

Singapore

+65.6768.5800

Shin-Yokohama, Japan

+81.45.476.0271

Chat with us:

[nvent.com/schroff](https://nvent.com/schroff)

### Middle East & India

Dubai, United Arab

Emirates

+971.4.378.1700

Bangalore, India

+91.80.6715.2001

Istanbul, Turkey

+90.216.250.7374

Chat with us:

[nvent.com/schroff](https://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY**

**ERICO**

**HOFFMAN**

**ILSCO**

**SCHROFF**

**TRACHTE**