We connect and protect

# PDU, 0U, 30A(24A)NA/32A Int, 380-415V, 3P Wye, 6 CB, (24)C13 (24)4-in-1

## Data Solutions

### CATALOG NUMBER

**EB0860**

The Basic PDU is a cost-effective, reliable power distribution solution. Premium hydraulic-magnetic circuit breakers operate consistently in high-temperature environments. The Basic PDU offers advanced features, such as color-coded locking IEC outlets, a slim chassis design, and toolless mounting backed by a 5-year hassle-free warranty.

### FEATURES

- Black Powder Coated Chassis
- IEC 62368 listed. RoHS, and REACH compliant. See drawing for additional information.

### PRODUCT ATTRIBUTES

- Product Family: Enlogic
- Type: Basic PDU
- Product Type: Socket Strip
- Socket Type: (24) C13/C15; (24) C13/C15/C19/C21
- Socket Quantity: 48
- Color: Black
- Switched Outlets: No
- Cable Length: 3000mm
- Circuit Breaker: 20 A, 1-pole, Hy-MagA
- Power Rating: 17.3 kVA North America; 22.1 kVA International
- Circuit Breaker Quantity: 6
- Nominal Power Output: 230VAC

Nominal Voltage: 415V

On/Off Switch Included: No

Amperage (Derated Amperage): 30 A (24 A) North America; 32 A International

Output Voltage: 208 – 230VAC

Rack Units: 0U

Plug Type: IEC 60309 530P6/532P6

Metering Type: None

Removable Input Cable: No

Material: Steel

Finish: Powder Coated

Height: 1490mm

Width: 56mm

Depth: 55mm

Package Quantity: 1

Input Cable Length: 3m

## ADDITIONAL PRODUCT DETAILS

Warranty : nVent Enlogic branded equipment provided shall be free from manufacturing defects for a period of five (5) years from the invoice date to the original purchaser.

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.