

Power Terminal, Tunnel-to-Tunnel, 800 A

Data Solutions

CATALOG NUMBER

SBTT-800



CERTIFICATIONS



FEATURES

Tinned copper block allows for copper or aluminum conductor connections

Accessible tunnels allow for easy connection of wire

Design allows for visual inspection of conductor and confirmation of connection

Voltage detection and measurement connection

Adjustable transparent cover

Modular snap-together blocks for building multi-pole power blocks

Easily clips onto DIN rail or mounts to panel with screws

SBLEC Power Terminals Fixing Accessory required for direct panel mount

RoHS compliant

Halogen free

PRODUCT ATTRIBUTES


Article Number: 561147
Material: Copper; Thermoplastic
Finish: Tinned
Max Current Rating, IEC: 1250A
Max Current Rating, UL/CSA: 760A
Short Term Withstand Current (Icw) 1s: 57.6kA
Peak Short Circuit Current (Ipk): 75kA
Short Circuit Current Rating (SCCR): 100kA
Max Working Voltage, IEC (Ui): 1000; 1500
Max Working Voltage, UL (Vin): 1000
Number of Tunnel Connections: 4
Tunnel Connection Compact Stranded Wire Size: (4) 95 – 240 mm²
Tunnel Connection Wire Size - Ferrule: (4) 50 – 185 mm²
Tunnel Connection Wire Size: (4) 3/0 – 500 kcmil
Depth (D): 2.95in
Height (H): 8.1in
Width (W): 4.53in
A: 4.25in
Unit Weight: 2.29lb
Certification Details: UL® 1059
Flammability Rating: UL® 94V-1
Complies With: IEC® 60947-7-1

ADDITIONAL PRODUCT DETAILS

Power terminal connections are interchangeable and can be used as line side or load side connections.

Design Guideline for Distribution Blocks, Power Blocks and Power Terminals										
Derating according to Ambient* Temperature (°F) to maintain working temperature of 185°F										
Ambient Temperature (°F)	86°	95°	104°	113°	122°	131°	140°	149°	158°	167°
Derating Coefficient (d)	1	1	1	0.94	0.88	0.82	0.75	0.67	0.58	0.47
*environment around the terminal blocks inside the enclosure										

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE