

# Power Block, Flexibar-Cable, 630 A IEC, Copper

## Data Solutions

### NÚMERO DE CATÁLOGO

### SBF630



nVent ERIFLEX Power Blocks are the main DIN mounted output/input devices for connection between primary and secondary switchboard, or main input/output connection for machine or industrial equipment (such as inverter, air conditioning machines, etc.). The high short circuit rated large cross section blocks offer time savings and reliability in every panel configuration. The complete Power Blocks range offers multiple connection types with up to four cables, nVent ERIFLEX Flexibar Advanced, or IBSB Advanced power braids.

### CERTIFICATIONS



### CARACTERÍSTICAS

Can be connected with round cross section cable or flat connection system like nVent ERIFLEX Flexibar Advanced or IBSB Advanced Insulated Braided Conductor

Compact power block with high short circuit current rating

Tinned copper or aluminum block allows for copper or aluminum conductor direct connections, or using ferrule

Screw retaining cover is hinged and removable

Design allows for visual inspection of conductor and confirmation of connection

Modular snap-together blocks for building multi-pole power blocks

Easily clips onto DIN rail or mounts to panel with screws

Voltage detection and measurement connection

95% fill ratio

RoHS compliant

Conforms to EN 45545 obtaining an HL3 classification for chapter R23 and HL2 classification for chapter R22

Halogen free plastic housing excluding the blue protection cover

## CARACTERÍSTICAS DO PRODUTO

---

Número do artigo: 561157

Acabamento: Tinned

Tipo: Flexibar-Cable

Typical Application Current Rating, IEC: 630A

Material: Copper; Termoplástico

Line Side Max Conductor Size, IEC: 240 mm<sup>2</sup>

Load Side Max Conductor Size, IEC: 500 mm<sup>2</sup>

Short Term Withstand Current (I<sub>cw</sub>) 1s: 60kA

Max Current Rating, Insulated Power Braid, IEC: 800A

Max Current Rating, nVent ERIFLEX Flexibar, IEC: 805A

Max Current Rating, UL: 545A

Peak Short Circuit Current (I<sub>pk</sub>): 51kA

Rated Conditional Short-Circuit Current (I<sub>cc</sub>): 24.3kA

Classificação de corrente de curto-circuito (SCCR): 100kA

Max Working Voltage, IEC (U<sub>i</sub>): 1000; 1500

Max Working Voltage, UL (V<sub>in</sub>): 1000

Line Side Number of Connections: 1

Line Side Insulated Power Braid Cross Section: 100mm<sup>2</sup>; 240mm<sup>2</sup>

Line Side nVent ERIFLEX Flexibar Size: 2x20x1 - 8x32x1

Load Side Compact Stranded Wire Size: 240 - 500 mm<sup>2</sup>

Load Side Number of Connections: 1

Load Side Wire Size: 400 – 1,000 kcmil

Profundidade (D): 89.4mm

Altura (H): 174.4mm

Largura (W): 54.2mm

Peso unitário: 1.39kg

Certification Details: UL® 1059

Em conformidade com: IEC® 60947-7-1

Classificação do gabinete: IP 20

Flammability Rating: UL® 94V-0

## DETALHES ADICIONAIS DO PRODUTO


---

SBF250 is UL® 1953 Listed when used with SB250SPCR. Max Working Voltage for UL 1953 applications is 1250 VAC/DC.

Blue protection cover is less than 7% of the overall product weight.

## DIAGRAMAS

---



## AVISO

---

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em [www.nVent.com](http://www.nVent.com) e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.



O nosso forte portefólio de marcas:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**