

Plug-In Unit U-Profile Front Panel for Handle Form 1



U-profile front panel. Enables the assembly of form 1 trapezoid form extraction handle. The front panel can be shielded with a textile gasket.

CERTIFICATIONS



CARACTERISTICI

Al profile, front anodized, rear conductive

Front panel, U-profile, shieldable

Alignment pin pressed-in, stainless steel

SPECIFICAȚII

Material:	Aluminiu
Finish:	Anodized; Passivated
Accessory Type:	Front panel
Product Type:	Front Panel
Type:	Front Panel with Handle (PIU)
EMC Shielding:	No (Retrofittable)

Table 1/3

Număr de catalog	Rack Height	Rack Width	Package Quantity	Handle Type	Mounting	Gasket Type
------------------	-------------	------------	------------------	-------------	----------	-------------

30848-461	3U	4HP	1	Trapezoid, Type 1	Screw-on Front	Textile EMC
30848-465	3U	8HP	1	Trapezoid, Type 1	Screw-on Front	Textile EMC
30848-474	6U	12HP	1	Trapezoid, Type 1	Screw-on Front	Textile EMC
30848-466	3U	10HP	1	Trapezoid, Type 1	Screw-on Front	Textile EMC
30848-473	6U	10HP	1	Trapezoid, Type 1	Screw-on Front	Textile EMC
30848-463	3U	6HP	1	Trapezoid, Type 1	Screw-on Front	Textile EMC
30848-472	6U	8HP	1	Trapezoid, Type 1	Screw-on Front	Textile EMC
30848-467	3U	12HP	1	Trapezoid, Type 1	Screw-on Front	Textile EMC
30848-468	6U	4HP	1	Trapezoid, Type 1	Screw-on Front	Textile EMC
30848-470	6U	6HP	1	Trapezoid, Type 1	Screw-on Front	Textile EMC

Table 2/3

Număr de catalog	Front Finish	Rear Finish	Treated Edges	Complies With	Depth (D)	Height (H)
30848-461	Anodized	Conductive	No	IEC 60297-3-101, IEEE 1101.1/11	2.5mm	128.4mm
30848-465	Anodized	Conductive	No	IEC 60297-3-101, IEEE 1101.1/11	2.5mm	128.4mm
30848-474	Anodized	Conductive	No	IEC 60297-3-101, IEEE 1101.1/11	2.5mm	261.8mm
30848-466	Anodized	Conductive	No	IEC 60297-3-101, IEEE 1101.1/11	2.5mm	128.4mm
30848-473	Anodized	Conductive	No	IEC 60297-3-101, IEEE 1101.1/11	2.5mm	261.8mm
30848-463	Anodized	Conductive	No	IEC 60297-3-101, IEEE 1101.1/11	2.5mm	128.4mm
30848-472	Anodized	Conductive	No	IEC 60297-3-101, IEEE 1101.1/11	2.5mm	261.8mm

Număr de catalog	Front Finish	Rear Finish	Treated Edges	Complies With	Depth (D)	Height (H)
30848-467	Anodized	Conductive	No	IEC 60297-3-101, IEEE 1101.1/11	2.5mm	128.4mm
30848-468	Anodized	Conductive	No	IEC 60297-3-101, IEEE 1101.1/11	2.5mm	261.8mm
30848-470	Anodized	Conductive	No	IEC 60297-3-101, IEEE 1101.1/11	2.5mm	261.8mm

Table 3/3

Număr de catalog	Width (W)
30848-461	20mm
30848-465	40.3mm
30848-474	60.6mm
30848-466	50.5mm
30848-473	50.5mm
30848-463	30.1mm
30848-472	40.3mm
30848-467	60.6mm
30848-468	20mm
30848-470	30.1mm

DETALII SUPLIMENTARE DESPRE PRODUS

Please order EMC profile seal separately.

Please take into consideration that deliveries may be carried out in the stated SPQs (SPQ, e.g. 5 pieces, 10 pieces, 50 pieces, etc.). Differing order quantities (e.g. 2 pieces) may be changed to the next possible delivery quantity = Standard Pack Quantity.

