

Outdoor Comline ECL Cabinet



Telecom and Railway applications require sophisticated electronics in outdoor setups. nVent SCHROFF Outdoor cabinets shield such electronic components from extreme weather and vandalism ensuring operational continuity.

CERTIFICATIONS



CARACTERISTICI

IP 55

Heat dissipation through natural convection

Single wall, lightweight aluminium cabinet

SPECIFICAȚII

Material: Aluminiu

Table 1/3

Număr de catalog	Product Type	Product Family	Rack Height	Height	Width	Depth
12349-003	Outdoor Cabinet	Comline ECL	18U	900mm	700mm	600mm
12349-001	Outdoor Cabinet	Comline ECL	12U	600mm	600mm	500mm
12349-010	Outdoor Cabinet	Comline ECL	18U	900mm	600mm	500mm

Număr de catalog	Product Type	Product Family	Rack Height	Height	Width	Depth
12349-011	Outdoor Cabinet	Comline ECL	18U	900mm	700mm	600mm
12349-009	Outdoor Cabinet	Comline ECL	12U	600mm	600mm	500mm
12349-004	Outdoor Cabinet	Comline ECL	25U	1200mm	700mm	600mm
12349-012	Outdoor Cabinet	Comline ECL	25U	1200mm	700mm	600mm
12349-002	Outdoor Cabinet	Comline ECL	18U	900mm	600mm	500mm

Table 2/3

Număr de catalog	Wall Type	Door Type	Access	Cooling	EMC Shielding	Complies With
12349-003	Single Walled	Single Door	Front	Natural Convection	No	IEC 61969-1, IEC 61969-2, IEC 60917-1, IEC 60917-2, ETS 300119, IEC 60529, DIN EN 50178, VDE 0160
12349-001	Single Walled	Single Door	Front	Natural Convection	No	IEC 61969-1, IEC 61969-2, IEC 60917-1, IEC 60917-2, ETS 300119, IEC 60529, DIN EN 50178, VDE 0160
12349-010	Single Walled	Single Door	Front	Natural Convection	No	IEC 61969-1, IEC 61969-2, IEC 60917-1, IEC 60917-2, ETS 300119, IEC 60529, DIN EN 50178, VDE 0160
12349-011	Single Walled	Single Door	Front	Natural Convection	No	IEC 61969-1, IEC 61969-2, IEC 60917-1, IEC 60917-2, ETS 300119, IEC 60529, DIN EN 50178, VDE 0160

Număr de catalog	Wall Type	Door Type	Access	Cooling	EMC Shielding	Complies With
12349-009	Single Walled	Single Door	Front	Natural Convection	No	IEC 61969-1, IEC 61969-2, IEC 60917-1, IEC 60917-2, ETS 300119, IEC 60529, DIN EN 50178, VDE 0160
12349-004	Single Walled	Single Door	Front	Natural Convection	No	IEC 61969-1, IEC 61969-2, IEC 60917-1, IEC 60917-2, ETS 300119, IEC 60529, DIN EN 50178, VDE 0160
12349-012	Single Walled	Single Door	Front	Natural Convection	No	IEC 61969-1, IEC 61969-2, IEC 60917-1, IEC 60917-2, ETS 300119, IEC 60529, DIN EN 50178, VDE 0160
12349-002	Single Walled	Single Door	Front	Natural Convection	No	IEC 61969-1, IEC 61969-2, IEC 60917-1, IEC 60917-2, ETS 300119, IEC 60529, DIN EN 50178, VDE 0160

Table 3/3

Număr de catalog	Package Quantity	Finish
12349-003	1	Vopsit Pulbere
12349-001	1	Vopsit Pulbere
12349-010	1	Vopsit Pulbere
12349-011	1	Vopsit Pulbere
12349-009	1	Vopsit Pulbere
12349-004	1	Vopsit Pulbere
12349-012	1	Vopsit Pulbere
12349-002	1	Vopsit Pulbere

AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Portofoliul nostru puternic de mărci:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE