

# Strömterminal, flexiblar-4 kablar, 1 600 A IEC, aluminium

## Data Solutions

### KATALOGNUMMER

**SBF4C1600AL**



nVent ERIFLEX Power Blocks are the main DIN mounted output/input devices for connection between primary and secondary switchboard, or main input/output connection for machine or industrial equipment (such as inverter, air conditioning machines, etc.). The high short circuit rated large cross section blocks offer time savings and reliability in every panel configuration. The complete Power Blocks range offers multiple connection types with up to four cables, nVent ERIFLEX Flexibar Advanced, or IBSB Advanced power braids.

### CERTIFIERINGAR



### DESIGN

Uppfyller RoHS

Halogenfri

Can be connected with round cross section cable or flat connection system like nVent ERIFLEX Flexibar Advanced or IBSB Advanced Insulated Braided Conductor

Compact power block with high short circuit current rating

Tinned copper or aluminum block allows for copper or aluminum conductor direct connections, or using ferrule

Screw retaining cover is hinged and removable

Design allows for visual inspection of conductor and confirmation of connection

Modular snap-together blocks for building multi-pole power blocks

Easily clips onto DIN rail or mounts to panel with screws

Voltage detection and measurement connection

95% fill ratio

Conforms to EN 45545 obtaining an HL3 classification for chapter R23 and HL2 classification for chapter R22

## PRODUKTATTRIBUT

Artikelnummer: 561177

Yta: Förtentat

Typ: Flexibar-4-kablar

Märkström vid vanlig tillämpning, IEC: 1600A

Material: Aluminium; Termoplast

Max. ledarstorlek för ledningssida, IEC: 800 mm<sup>2</sup>

Max. ledarstorlek för belastningssida, IEC: (4) 300 mm<sup>2</sup>

Kortsiktig hållström (I<sub>cw</sub>) 1s: 96kA

Max. märkström, IEC: 1940A

Max. märkström, UL/CSA: 1680A

Maximal kortslutningsström (I<sub>pk</sub>): 105kA

Nominell kortslutningsmärkström (I<sub>cc</sub>): 50kA

Kortslutningsströmsvärde (SCCR): 100kA

Max. arbetsspänning, IEC (U<sub>i</sub>): 1000; 1500

Max. arbetsspänning, UL (V<sub>in</sub>): 1000

Antal anslutningar på ledningssida: 1

nVent ERIFLEX Flexibar-storlek på ledningssida: 6X50X1 - 10X80X1

DLO-ledningsstorlek för ledningssida: #2 - 373 kcmil

Compact i flertrådsstorlek för belastningssida: (4) 35–300 mm<sup>2</sup>

Antal anslutningar på belastningssida: 4

Flertrådsstorlek för belastningssida – hylsa: (4) 35–300 mm<sup>2</sup>

Ledarstorlek för belastningssida: (4) #2 - 600 kcmil

Djup (D): 112mm

Höjd (H): 176mm

Bredd (W): 99mm

Enhetsvikt: 1.29kg

Certifieringsinformation: UL® 1953

Uppfyller: IEC® 60947-7-1

Kapslingsklass: IP20

Brandklassning: UL® 94V-0


YTTERLIGARE PRODUKTINFORMATION

SBF250 is UL® 1953 Listed when used with SB250SPCR. Max Working Voltage for UL 1953 applications is 1250 VAC/DC.

Blue protection cover is less than 7% of the overall product weight.

| Design Guideline for Distribution Blocks, Power Blocks and Power Terminals              |     |     |     |      |      |      |      |      |      |      |
|-----------------------------------------------------------------------------------------|-----|-----|-----|------|------|------|------|------|------|------|
| Derating according to Ambient* Temperature (°C) to maintain working temperature of 85°C |     |     |     |      |      |      |      |      |      |      |
| Ambient Temperature (°C)                                                                | 30° | 35° | 40° | 45°  | 50°  | 55°  | 60°  | 65°  | 70°  | 75°  |
| Derating Coefficient (d)                                                                | 1   | 1   | 1   | 0.94 | 0.88 | 0.82 | 0.75 | 0.67 | 0.58 | 0.47 |
| *environment around the terminal blocks inside the enclosure                            |     |     |     |      |      |      |      |      |      |      |

DIAGRAMS



WARNING

nVent produkter ska installeras och användas endast så som anges i nVents bruksanvisning och utbildningsmaterial. Bruksanvisningar är tillgängliga på [www.nvent.com](http://www.nvent.com) och från din nVent kundtjänstrepresentant. Felaktig installation, missbruk, felapplicering eller annan brist i att helt följa nVents instruktioner och varningar kan orsaka att produkten brister, egendomsskador, allvarliga kroppsskador och dödsfall och/eller ogiltigförklara din garanti.



Vårt starka utbud av varumärken:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**